Tyco Electronics

Our commitment. Your advantage.

- # Products

  - By Type
    - Connectors
    - Electromechanical Components
    - Electronic Modules
    - Fiber Optics
    - Filters
    - Identification & Labeling
    - Passive Components
    - Power Sources
    - RF & Microwave Products
    - Tooling Products
    - Touch Screen Displays
    - Tubing, Molded and Harnessing Products
    - Wire, Cable and Cable Assemblies
    - List all product types...
  - By Industry
    - Aerospace & Defense Products
    - Appliance
    - Automotive
    - Communications
    - Computer & Consumer Electronics
    - Industrial & Commercial
    - Instrumentation & Medical
  - By Brand
  - A to Z
  - Product News

- # Documentation

  - Find Documents & Drawings
  - Find CAD Models
  - SPICE/Electrical Models
  - NAFTA Certificate of Origin
  - White Papers

- # Resources

  - RoHS Compliance & Alternates
  - Cross Reference Products
  - Compare Multiple Products
  - Check Distributor Inventory
  - Find Authorized Distributors

- # My Account

  - Sign In
  - Register

- # Customer Support

  - Support
  - RoHS Support Center
  - Glossary of Terms
  - eBulletin Newsletter

9400-04T1999 Product Details

Mid-Range Plug-in/Panel Mount General Purpose Relays

Converted to EU RoHS but not ELV Compliant (Statement of Compliance)

9400-04T1999

✔ Active

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Compare Products
- Contact Us About This Product

Product Highlights:

- 9400 Series
- Contact Arrangement = 1 Form Z, SPDT - 2 N/C & 2 N/O, DB DM (jumpered to wire as 1 Form C)
- Contact Current Rating = 8 - 12 Amps.
- Monostable Coil Magnetic System
- Input Voltage = 120 VAC

View all Features | Find Similar Products

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- 9400 Power Relay 1-pole, 8-12 FLA AC or DC Coil (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Termination Type = .250 x .032 Quick Connect Terminals

Electrical Characteristics:

- Contact Current Rating (Amps.) = 8 12
- Input Voltage (VAC) = 120
- Actuating System = AC

Body Related Features:

- Series = 9400

Contact Related Features:

- Mounting Options = Special I Bracket with mounting holes on 2.156" (54.76mm) centers
- Enclosure = Open
- FCC Part 68 Isolation = No
- Relay Type = General
- Contact Material = Silver Alloy
- Approx. Dimensions (L x W x H) (mm[in]) = 46.8 x 32.1 x 38.1 [1.840 x 1.260 x 1.500]
- Contact Type = Power
- Approved Standards = UL Recognized for Canada and US
- Number of Poles = 1

Configuration Related Features:

- Contact Arrangement = 1 Form Z, SPDT - 2 N/C & 2 N/O, DB DM (jumpered to wire as 1 Form C)
- Coil Magnetic System = Monostable
- Coil Suppression Diode = Without
- Coil Selection Criteria = Nominal Voltage
- Coil Latching = Without
- LED Indicator = Without

Industry Standards:

- RoHS/ELV Compliance = RoHS/Not ELV Compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS not ELV directives

Packaging Related Features:

- Packaging Method = Bulk

Other:

- Brand = Products Unlimited