



CP16DH10IP6474BF Product Details

[Share](#) [Print](#) [Email](#)


Variable Resistors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K Ω
- Resistance = 470K Ω
- Power Rating = .10 W

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

CP16DH10IP6474BF

(5-1676003-6)

TE Internal Number: 5-1676003-6

Active

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SPINDLE OPERATED POTENTIOMETER SERIES CP16](#) (PDF, English)

Catalog Pages/Data Sheets:

- [1309350_PASSIVE_COMPONENT](#) (PDF, English)
- [Spindle Operated Potentiometers - Type CP16 Series -...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Variable Resistor
- Resistor Type = Potentiometer
- Element = Carbon
- Sealed = No

Electrical Characteristics:

- Resistance Selection (Ω) = K
- Resistance (Ω) = 470K
- Power Rating (W) = 0.10
- Tolerance (%) = 20

Termination Features:

- Termination Type = PCB Terminations
- Termination Post Orientation = In Line

Body Features:

- Shaft Style = Serrated, 6 x 45mm
- Package, Component Size = 16mm Sq.

Configuration Features:

- Sections = Dual
- Adjustment Location = Side
- Adjustment Style = Spindle
- Operating Function = Single Turn

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Coefficient (ppm/°C) = 1000

Other:

- Series = CP16
- Brand = Citec
- Comment = Nuts fitted.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility
Plan](#)