

# TSB23006DS Product Details

[Live Product Chat](#)



## Europa Terminal Blocks

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

### Product Highlights:

- Terminal Block
- 8.00 mm Centerline
- Number of Circuits = 6
- Wire Range = 0.12-3.00; [26-12] mm [AWG]
- With Wire Protection

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

## TSB23006DS

(9-1437387-3)

TE Internal Number: 9-1437387-3

**Superseded**

[Search for Replacement Parts](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- None Available

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- [Product Type](#) = Terminal Block
- [Number of Circuits](#) = 6
- [Integrated Fuse](#) = No
- Color = Natural
- Screw Size = M3 Screw
- Screw Material = Steel
- CSA File No. = LR28387
- UL Recognized = File No. E60677

### Mechanical Attachment:

- Screw Plating = Bright Zinc/Chrome

### Electrical Characteristics:

- Current Rating (Amps.) = 30
- Voltage Rating (VAC) = 250
- Wire Protector Material = Stainless Steel

### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 8.00 [0.315]
- [Wire Range \(mm \[AWG\]\)](#) = 0.12-3.00; [26-12]
- [Wire Protection](#) = With
- [Ground](#) = Without
- [Series](#) = TSB230
- Flammability Rating = UL 94V-2

### Contact Related Features:

- Contact Base Material = Brass
- Contact Mating Area Plating Material = Tin

### Housing Related Features:

- Housing Material = Polyamide

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

### Conditions for Usage:

- [Temperature Range \(?C\)](#) = 105

### Other:

- Brand = Buchanan