




Our commitment. Your advantage.

- [Products](#)
- [Documentation](#)
- [Resources](#)
- [My Account](#)
- [Customer Support](#)

[Home](#) > [Products](#) > [By Type](#) > [Resistors](#) > [Product Feature Selector](#) > Product Details

404806392008 Product Details

[Live Product Chat](#)



404806392008
(1623837-8)

TE Internal Number: 1623837-8

[Active](#)

Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Variable Resistor
- Resistor Type = Trimmer
- Resistance Selection = K ?
- Resistance = 2K ?
- Power Rating = .50 W

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • Professional Trimmers - Type 4295 Series - Tyco Elec... (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Variable Resistor • Resistor Type = Trimmer • Resistance (?) = 2K • Element = Cermet • Sealed = Yes • Mount Angle = Horizontal • Termination Type = PCB Terminations <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Resistance Selection (?) = K • Power Rating (W) = 0.50 • Tolerance (%) = 10 <p>Termination Related Features:</p> <ul style="list-style-type: none"> • Termination Post Orientation = 5.0 x 5.0 <p>Body Related Features:</p> <ul style="list-style-type: none"> • Series = 4295 • Package, Component Size = 10 	<p>Configuration Related Features:</p> <ul style="list-style-type: none"> • Sections = Single • Adjustment Location = Top • Adjustment Style = Screwdriver Slot • Operating Function = Single Turn <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Converted to comply with RoHS directive <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Coefficient (ppm/°C) = 100 <p>Other:</p> <ul style="list-style-type: none"> • Brand = Citec

[Provide Website Feedback](#) | [Need Help?](#)