



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Circuit Application: **Signal**

Features

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Model / Part #2-1393531-9
V23535A3280C161=BKMOD422 FEDER




TE Model / Part #3-1393531-4
V23535A3280C341=BKMOD422 FEDER



TE Model / Part #87190-1
LOCKING CLIP CONT ASSY .025 SQ



TE Model / Part #926209-8
2X8P LOCK-CLIP GEH



TE Model / Part #3-1393561-4
V42254A6106L 1=SUB D KONTAKTH



TE Model / Part #3-1393531-1
V23535A3280C201=BKMOD422 FEDER



TE Model / Part #926209-6
2X6P LOCK-CLIP GEH



TE Model / Part #926899-3
UNIV-MNL SPLIT ST



TE Model / Part #1604113-1
AMP Power Contact 15A,STRIP,SILVER



TE Model / Part #926209-2
LOCKING CLIP HSG.

Documents

Product Drawings

[C42334A 422C326=BKMOD 422 BUEG](#)

English

[C42334A 422C326=BKMOD 422 BUEG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1393558-2_A.2d_dxf.zip](#)

English

Customer View Model



[ENG_CVM_CVM_1-1393558-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1393558-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.