



Have a Question?
Chat with a Product Information Specialist

What can we help you find?

- [Products](#)
- [Industries](#)
- [Resources](#)
- [About TE](#)
- [My Account](#)
- [Innovation](#)
- [Support Center](#)

CP16SH10IP06473F Product Details

- [Share](#)
- [Print](#)
- [Email](#)



CP16SH10IP06473F

TE Internal Number: 6-1676003-6
✔ Active

Variable Resistors

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K Ω
- Resistance = 47K Ω
- Power Rating = .20 W

[View all Features](#)

Quick Links

- [▶ Pricing & Availability](#)
- [▶ Search for Tooling](#)
- [▶ Product Feature Selector](#)
- [▶ Contact Us About This Product](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • SPINDLE OPERATED POTENTIOMETER SERIES CP16 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • 1309350_PASSIVE_COMPONENT (PDF, English) • Spindle Operated Potentiometers - Type CP16 Series - ... (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Variable Resistor • Resistor Type = Potentiometer • Element = Carbon • Sealed = No <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Resistance Selection (Ω) = K • Resistance (Ω) = 47K • Power Rating (W) = 0.20 • Tolerance (%) = 20 <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Type = PCB Terminations • Termination Post Orientation = In Line <p>Body Features:</p> <ul style="list-style-type: none"> • Shaft Style = Serrated, 6 x 45mm • Package, Component Size = 16mm Sq. 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Sections = Single • Adjustment Location = Side • Adjustment Style = Spindle • Operating Function = Single Turn <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Coefficient (ppm/°C) = 500 <p>Other:</p> <ul style="list-style-type: none"> • Series = CP16 • Brand = Citec • Comment = Nuts fitted.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

[Careers](#)

[Site Map](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility
Plan](#)

Keep Me Informed

