



Alcoswitch | Alcoswitch Gemini A

TE Internal #: 1-1825136-7

Alcoswitch Gemini A, Toggle Switches, Single Pole - Double Throw Configuration (Pole-Throw), Sealed Toggle Switch, Copper, Gold, Terminal Seal (Epoxy)

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**

Sealed Toggle Switch: **Yes**

Contact Base Material: **Copper**

Switch Contact Plating Material: **Gold**

Process Sealed: **No**

## Features

### Product Type Features

Product Type	Switch
Sealed Toggle Switch	Yes
Toggle Style	Baton Short
Toggle Switch Type	Toggle
Toggle Actuation	Vertical

### Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On

### Electrical Characteristics

Dielectric Strength	1000 VAC
Insulation Resistance	1000 MΩ
Contact Resistance	10 mΩ
Toggle Switch Voltage Rating	120 VAC

### Body Features

Actuator Finish	Nickel
Toggle Switch Seal Type	Terminal Seal (Epoxy)
Bushing Style	Unthreaded

### Contact Features



Contact Base Material	Copper
Switch Contact Plating Material	Gold
Toggle Switch Contact Current Rating	5 A

#### Termination Features

Termination Type	Vertical Right Angle
------------------	----------------------

#### Mechanical Attachment

Toggle Switch Mounting Type	Through Hole
-----------------------------	--------------

#### Housing Features

Process Sealed	No
----------------	----

#### Dimensions

Toggle Length	6.86 mm[.27 in] .28 in
---------------	---------------------------

#### Industry Standards

UL Flammability Rating	UL 94V-1
------------------------	----------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Pb (3.7% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Model / Part # 5-1825136-9  
A108P3ZQ04



TE Model / Part # 4-1825136-9  
A101SYZQ04



TE Model / Part # 1825136-7  
A101KZQ04




TE Model / Part # 4-1825136-5  
A101SYCQ04



TE Model / Part # 4-1825136-3  
A101SYAQ04

## Also in the Series | Alcoswitch Gemini A



Toggle Switches(97)


## Customers Also Bought



TE Model / Part #1833011-1  
STD SCHRACK RZF Power Relays



TE Model / Part #5-2176331-9  
CRGP 2512 680K 1%



TE Model / Part #3-2176314-8  
MELF SMA\_A 180R 1% 50PPM 0102 0.3  
W



TE Model / Part #7-1879212-5  
CPF 0402 13R7 0.1% 25PPM 1K RL  
W



TE Model / Part #1-1825138-8  
A201SD9AV2Q04



TE Model / Part #1-2232001-2  
2P, RAST 5 Tab Header, THV, black,  
silver



TE Model / Part #1825137-3  
A103MD9AG04



TE Model / Part #104071-8  
06 SYSTEM 50 HDR SRST SHRD



TE Model / Part #1571990-4  
TSPD11CGRA004



TE Model / Part #1825142-6  
AE101MD1AV2Q04

## Documents

### Product Drawings

[A101MD9AV2Q04](#)

English

### Datasheets & Catalog Pages

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English

[GEMINI\\_SERIES\\_SWITCHES\\_QUICK\\_REF\\_GUIDE\\_2-1773458-5](#)

English