


COIL: @ 25°C	
RESISTANCE	7500 OHMS ± 10%
NOMINAL VOLTAGE	115.0 VDC
MUST OPERATE	63.0 VDC
MUST RELEASE	5.0 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 20 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 13 MS MAX.
	RELEASE TIME 5 MS MAX.
	CONTACT BOUNCE 5 MS MAX. (NC)
	2 MS MAX. (NO)

**CUSTOMER DATA SHEET**



CONTACT RATING:	10 AMPS 30 VDC RES.
	10 AMPS 115 VAC 400 Hz. 6A 30 VDC
	INDUCTIVE 100,000 OPERATIONS

DR. R.B. 9/10/93 CK 9/10/93



CUST. HI-G  
CUST. NO. 2T-1A-215

TYPE '07' RELAY

B07B032BZ1-8002