



+ CONNECTORS

TRANSISTOR SOCKETS



✓ Active

TE CONNECTIVITY (TE)

8058-1G24=TO5 SOCKET 200 CIRC

Augat | AD

8058-1G24

TE Internal Number: 1437508-9

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Number of Positions 4

Profile Low

Package TO-5

Lead Size Accepted .41 mm [.016 in]

Termination Method Printed Circuit

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

SOCKET, 8 PIN PRINTED CIRCUIT

PDF (TIFF AVAILABLE)

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration Contact

Profile Low

Package TO-5

Product Type Socket

Configuration Features

Number of Positions 4

Body Features

Lead Size Accepted .41 mm [.016 in]

Color Black

Insulator Material Fluoropolymer

Sleeve Plating Material Gold

Sleeve Material Brass

Contact Features

Terminal Plating Gold

Termination Method Printed Circuit

Pin Diameter 5.08 mm [.2 in]

Terminal Material Beryllium Copper

Socket Type Transistor

Usage Conditions

Operating Temperature Range (°C) -55 – 125

Industry Standards

Insulator Flammability Rating UL 94V-0

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

