

Part Number: 120103-0001

D-Sub Connector with Diagnostics LEDs and Programming Port, 90° Angle



Status: Active
Series: [120103](#)
Category: Field Attachable / Accessories
Overview: [Brad@PROFIBUS Solutions](#)
Old Part Number: PA9D01-42

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)
[Email this page](#)

Go to **Part Detail** ▼

Specifications & Other Documents:

[Datasheet](#)

Sales Drawings, 3D Models, and Brochures

[Drawing \(PDF\)](#)

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

[EU RoHS:](#) ELV and RoHS Compliant

[China RoHS:](#)

[REACH SVHC:](#)

[Low-Halogen Status:](#) Not Reviewed

[RoHS Certificate of Compliance \(PDF\)](#)

[Multiple Part Product Compliance Form](#)

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ **General**

Status	Active
Category	Field Attachable / Accessories
Series	120103
IP Rating	IP67
Overview	Brad@PROFIBUS Solutions
Product Name	Profibus*
Type	Field Attachable Connector

▼ **Physical**

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
Keyway	None
Material - Connector Body	Die-Cast Zinc
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Orientation	90° Angle
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A

▼ **Electrical**

(Please review the Product Specification for specific details.)	
Current - Maximum per Contact	4A
Voltage - Maximum	30V

▼ **Material Info**

Old Part Number	PA9D01-42
-----------------	-----------

▼ **Reference - Drawing Numbers**

Sales Drawing	SD-120103-003
---------------	---------------

Molex Connectors

Wire-to-Board
 Board-to-Board
 Wire-to-Wire
 Input/Output (IO)
 FFC/FPC
 Sockets

Other Products

Antennas
 Industrial Automation
 Membrane Switches
 Copper Flex
 PCB Assemblies
 Woodhead Electrical
 Solid State Lighting
 Fiber Optic

Resources

Catalog
 Cross-Reference
 Industries
 Literature
 Product Name

Company Info

About Us
 Careers
 Contact Us
 ecocare
 Investors
 Press Room
 Shows & Events

Other Info

Feedback
 Help
 Legal Disclaimer
 Privacy Policy
 Sitemap

Stay Connected with Molex:

