

[Skip to content](#)

[Corporate Home](#) | [Electronic Components](#) | [Segments](#) | [Who We Are](#)

Worldwide



Our commitment. Your advantage.

Search

By:



[Sign In](#) | [Register \(Why Register?\)](#)

[Products](#)



- Connectors
- Electromechanical Components
- Electronic Modules
- Fiber Optics
- Filters
- Identification Labeling Products
- Passive Components
- Power Sources
- RF & Microwave Products
- Tooling Products
- Touch Screen Displays
- Tubing, Molded and Harnessing Products
- Wire, Cable and Cable Assemblies
- List all Product Types

- [Aerospace & Defense](#)
- [Appliance](#)
- [Automotive](#)
- [Communications](#)
- [Computer & Consumer Electronics](#)
- [Industrial & Commercial](#)
- [Instrumentation & Medical Equipment](#)


[By Brand](#)

[A to Z](#)

- [Documentation](#)
 - [Find](#)
 - [Documents & Drawings](#)
 - [Find CAD Models](#)
 - [SPICE/Electrical Models](#)
 - [NAFTA Certificate of Origin](#)
 - [White Papers](#)
- [Resources](#)
 - [RoHS](#)
 - [Compliance & Alternates](#)
 - [Cross Reference Products](#)
 - [Compare Multiple Products](#)
 - [Check Distributor Inventory](#)
 - [Find Authorized Distributors](#)
- [My Account](#)
 - [Sign In](#)
 - [Register](#)
- [Customer Support](#)
 - [Support](#)
 - [RoHS Support Center](#)
 - [Glossary of Terms](#)
 - [eBulletin Newsletter](#)

[Home](#) > [Products](#) > [By Type](#) > [Switches](#) > [Product Feature Selector](#) > Product Details

6-1825011-2 Product Details



6-1825011-2
(ASF62G04)

✓ [Active](#)

Slide Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Number of Positions = 6
- Six Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Flush, Top
- Actuator Color = Natural
- ASE/F Series

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH ASF, AUTO-INSERTABLE, THRU-HOLE AND SUR...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Number of Positions](#) = 6
- Configuration (Pole-Throw) = Six Pole - Double Throw
- Actuator Style = Flush, Top
- Mount Angle = Vertical
- Grade = Telecom
- Termination Type = PC

Electrical Characteristics:

- Contact Rating = 300mA @ 115 VDC

Body Related Features:

- Actuator Color = Natural
- Series = ASE/F
- Mount Style = Through-Hole
- Switch Style = Auto-insertable
- PCB Tail Length (mm [in]) = 4.06 [0.160]
- Actuator Material = Polyester

Contact Related Features:

- Contact Plating = Gold
- Contact Material = Copper Alloy

Configuration Related Features:

- Terminal Configuration = Standard
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© [2007 Tyco Electronics Corporation All Rights Reserved](#)