


## 404806505010 Product Details

Share | Print | Email



**404806505010**  
(1-1623866-0)

TE Internal Number: 1-1623866-0

Active

[View 3D PDF](#)

### Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Variable Resistor
- Resistor Type = Trimmer
- Resistance Selection = K  $\Omega$
- Resistance = 10K  $\Omega$
- Power Rating = .75 W

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PROFESSIONAL TRIMMERS SERIES 433](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [Professional Trimmers - Type 433PW Series - Tyco Ele...](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version BA)
- [3D Model](#) (IGES, Version BA)
- [3D Model](#) (STEP, Version BA)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Trimmer
- [Element](#) = Cermet
- [Series](#) = 433
- [Sealed](#) = Yes
- [Termination Type](#) = PCB Terminations

#### Electrical Characteristics:

- Resistance Selection ( $\Omega$ ) = K
- [Resistance \( \$\Omega\$ \)](#) = 10K
- [Power Rating \(W\)](#) = 0.75
- [Tolerance \(%\)](#) = 10

#### Termination Features:

- [Termination Post Orientation](#) = 12.7 x 2.5

#### Body Features:

- [Package, Component Size](#) = 19

#### Configuration Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Side
- [Operating Function](#) = Multi Turn, Rectilinear

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = 250

#### Other:

- Brand = Citec

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

