

REV. 2 3/21/95


COIL: @ 25° C	
RESISTANCE	700 OHMS ± 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
MUST RELEASE	1.5 VDC

ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6 ± 1	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: \_\_\_\_\_  
 \_\_\_\_\_  
 \_\_\_\_\_

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS 30 VDC  
 RESISTIVE .75 AMP 30 VDC INDUCTIVE  
 100,000 OPERATIONS

DR. R.B. 3/21/95 CK 3/21/95



CUST. HI-G  
 CUST. NO. 2K-1B-126

TYPE 'HFW' RELAY

HFW1196S01