



What can we help you find?



Products Industries

Resources

About TE

Support Center

My Account

Home > Products > Relays > Product Feature Selector > Product Details

HMS1130S04L Product Details









HMS1130S04L (1617039-5)TE Internal Number: 1617039-5

Active

Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- HMS Half-Size Relay Series
- Input Voltage = 26.5 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rated Current = 2 A
- Non Polarized, Monostable Coil Magnetic System.

View all Features



- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- ▶ Contact Us About This Product







Documentation & Additional Information

Product Drawings:

None Available

Catalog Pages/Data Sheets:

RELAY (PDF, English)

Product Specifications:

None Available

Application Specifications:

None Available

Instruction Sheets:

None Available

CAD Files:

None Available

Additional Information:

Product Line Information

Related Products:

Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = HMS Half-Size Relay
- Termination Type = Solder Hook Terminals

Electrical Characteristics:

- Input Voltage (VDC) = 26.5
- Contact Rated Current (A) = 2
- Coil Polarity Protection Diode = Without
- Transistor Driver = Without
- Coil Resistance (Ω) = 1030
- MOSFET Driver = Without
- Coil Power Measurement = Milliwatts
- Coil Rated Power (mW) = 682
- Actuating System = DC
- Shock = 50G's, 11ms
- Vibration = 20G's, 10 to 2500Hz

Contact Features:

- Mounting Options = Chassis Mount
- Enclosure Type = Hermetically Sealed

Configuration Features:

List all Documents

- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Coil Magnetic System = Non Polarized, Monostable
- Coil Suppression Diode = Without

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M39016/44-028L
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not suitable for lead free processing
- Approved Standards = M39016 Qualified, L Level

Conditions for Usage:

Temperature Range (°C) = -65 - +125

Other:

Brand = CII

Corporate Information

Who We Are Investors News Room Supplier Portal

Careers

Quick Links

Check Distributor Inventory

Cross Reference

Find Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us Find a Phone Number Search Knowledge Base

Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates















