

REV. 0


DCO 17298

COIL: @ 25°C	700 OHMS ±10%
RESISTANCE	_____
NOMINAL VOLTAGE	22.0 VDC
MUST OPERATE	8.36 VDC
_____	_____
MUST RELEASE	5.0 VDC MAX., 0.63 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 20 g's
SHOCK	50 g's 11 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES: \_\_\_\_\_  
 \_\_\_\_\_  
 \_\_\_\_\_

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 2A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 9/21/01

CK. 716 9-24-01

**Oil Technologies**  
 advanced control electronic solutions

CUST. GENICOM  
 CUST. NO. 3SAY5542H2 REV. \_\_\_\_\_

"HMS" RELAY

HMS1131S10