

1/5-SIZE RELAYS



✓ Active

> [See All Documentation](#)

TE CONNECTIVITY 3SBH5131K2 = RELAY

3SBH5131K2
TE Internal Number: 4-1617076-9

Not EU RoHS or ELV Compliant
[Find Compliant Alternatives](#)

Contact Arrangement **4 Form C, 4PDT, 4 C/O**

Input Voltage(VDC) **26.5**

Coil Suppression Diode **Without**

Contact Current Rating(A) **2**

Coil Resistance(Ω) **720**

> [See All Features](#)

North America ▼

Inventory does exist through Waldom (TE's master distributor) but is only available for purchase through a TE authorized distributor. Please contact your preferred authorized distributor for purchasing options.

[FIND AUTHORIZED DISTRIBUTORS](#) >

SAVE TO LIST	
CHECK FOR TOOLING	
FIND SIMILAR PRODUCTS	

DOCUMENTATION FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Relay Type	Military/Aerospace High Performance
	Product Type	Relay
	MOSFET Driver	Without
	Enclosure Type	Hermetically Sealed

Configuration Features	Transistor Driver	Without
------------------------	-------------------	----------------

Electrical Characteristics	Input Voltage(VDC)	26.5
	Coil Suppression Diode	Without
	Coil Resistance(Ω)	720
	Coil Power Rating (DC)(mW)	975
	Coil Magnetic System	Non-Polarized, Monostable
	Actuating System	DC
	Shock	100G's, 11ms
	Coil Power Measurement	Milliwatts
	Vibration	30G's, 10 – 3000Hz
	Coil Polarity Protection Diode	Without

Contact Features	Contact Arrangement	4 Form C, 4PDT, 4 C/O
	Contact Current Rating(A)	2

Termination Features	Termination Type	Solder Hook Terminal
----------------------	------------------	-----------------------------

Mechanical Attachment	Mounting Type	Chassis Mount
-----------------------	---------------	----------------------

Usage Conditions	Operating Temperature Range(°C)	-65 – 200
------------------	---------------------------------	------------------

Product Compliance
[Statement of Compliance](#)
PDF
[VIEW ALL PRODUCT COMPLIANCE](#)

COMPATIBLE

No compatible products found for 3SBH5131K2