



HARNESSING

HEAT SHRINK BOOTS



✓ Active

TE CONNECTIVITY (TE)

202A153-25-0

Raychem | CAP , CRPS

TE Internal Number: 806606-000

Alias ID: 202A153-25-0, 7-1196239-1

EU RoHS Compliant

EU ELV Compliant

Lipped No

Operating Temperature Range (°C) -75 – 150

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options S1048 Separate Adhesive, -55°C – 105°C (-67°F – 221°F), S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F)

Material Systems Code 25

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Boot, Straight, Overexpanded

PDF

English

Product Specifications

Product Specification

Thermofit Elastomeric Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable

PDF

English

-25 MOULDED PARTS

PDF

English

Product Environmental Compliance

Safety Data Sheet

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

EPS Heat Shrinkable Polymeric Products

PDF

Danish

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped No

Body Features

Material Systems Code 25

Adhesive Pre-Coat No

Material Modified Elastomer

Dimensions

Cable Diameter Range 8.6 – 26.2 mm [.339 – 1.031 in]

Wire/Cable Outside Diameter .39 in, .43 in, .433 in, .47 in, .55 in, .63 in, .7 in, .71 in, 10 mm, 11 mm, 12 mm, 14 mm, 16 mm, 18 mm

Usage Conditions

Operating Temperature Range (°C) -75 – 150

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No

Approved Standards BS-G-198-5-DE, DEF Std 59-97 Issue 3 Type DE, IEC 62329-3-102, MIS-34867

Other

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options S1048 Separate Adhesive, -55°C – 105°C (-67°F – 221°F), S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F)

Adhesive Type Adhesive Purchased Separately

Statement of Compliance

Statement of Compliance

PDF