


SIGNAL RELAYS



✓ Active

[See All Documentation](#)

TE CONNECTIVITY V23054D1021F104

Axicom | Cradle Relay S

9-1393812-4

TE Internal Number: 9-1393812-4
 Alias ID: V23054D1021F104

Converted to EU RoHS/ELV Compliant

Contact Voltage Rating **250VAC[260VDC]**

Coil Power Rating (DC)(mW) **736**

Insulation Initial Resistance(MΩ) **1000**

Mounting Type **Screw Mount, Socket**

Terminal Type **Plug-In, Solder**

[See All Features](#)

North America ▼

Contact us to request pricing, availability and customization options.

[REQUEST ADDITIONAL INFORMATION](#)

GET SAMPLE	
SAVE TO LIST	
CHECK FOR TOOLING	
FIND SIMILAR PRODUCTS	

DOCUMENTATION [FEATURES](#)

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Relay Style	Cradle S Relay
	Product Type	Relay
	Relay Type	Cradle S Relay V23054/V23062

Electrical Characteristics	Contact Voltage Rating	250VAC[260VDC]
	Coil Power Rating (DC)(mW)	736
	Insulation Initial Resistance(MΩ)	1000
	Contact Switching Voltage (Max)	250VAC[260VDC]
	Coil Magnetic System	Monostable, DC
	Insulation Initial Dielectric Between Coil/Contact Class	500 – 1000 V
	Insulation Initial Dielectric Between Adjacent Contacts(Vrms)	100
	Insulation Initial Dielectric Between Contacts and Coil(Vrms)	1000
	Contact Limiting Making Current(A)	5
	Insulation Initial Dielectric Between Open Contacts(Vrms)	500
	Actuating System	DC
	Contact Limiting Short-Time Current(A)	5
	Contact Limiting Continuous Current(A)	5
	Coil Resistance(Ω)	1050
	Contact Limiting Breaking Current(A)	5
	Power Consumption(mW)	800
Coil Power Rating Class	800 – 1000 mW	
Coil Type	Monostable	

Body Features	Weight	25g[.881oz]
---------------	--------	--------------------

Contact Features	Terminal Type	Plug-In, Solder
	Contact Current Rating(A)	2
	Contact Arrangement	4 Form C (CO)
	Contact Material	Ag
	Contact Number of Poles	2
	Contact Current Class	2 – 5 A
	Contact Plating Material	Gold Flash

Termination Features	Termination Type	Solder Terminals
----------------------	------------------	-------------------------

Mechanical Attachment	Mounting Type	Screw Mount, Socket
-----------------------	---------------	----------------------------

Dimensions	Length Class (Mechanical)	25 – 30 mm
	Width Class (Mechanical)	16 – 20 mm
	Length	30mm[1.181in]
	Width	19mm[.748in]
	Height Class (Mechanical)	25 – 30 mm
	Height	30mm[1.181in]

Usage Conditions	Environmental Category of Protection	RTI
	Operating Temperature Range(°C)	-40 – 70
	Environmental Ambient Temperature (Max)	70°C[158°F]
	Environmental Ambient Temperature Class	50 – 70°C

Operation/Application	Performance Type	Standard
-----------------------	------------------	-----------------

Packaging Features	Packaging Method	Box/Carton
--------------------	------------------	-------------------

Product Compliance [Statement of Compliance PDF](#)
[VIEW ALL PRODUCT COMPLIANCE](#)

COMPATIBLE

No compatible products found for 9-1393812-4