



X2

TE Internal #: 1367337-1


X2, Connector, Cable-to-Board, 70 Position, .031 in [.8 mm]

Centerline, Printed Circuit Board, Signal, Board Mount, -67 – 185 °F

[-55 – 85 °C], X2

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > X2



Pluggable I/O Product Type: **Connector**

Connector System: **Cable-to-Board**

Number of Positions: **70**

Centerline (Pitch): **.8 mm [.031 in]**

Sealable: **No**

Features

Product Type Features

Form Factor	X2
Connector & Housing Type	Receptacle
Pluggable I/O Product Type	Connector
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	70
---------------------	----

Contact Features

Contact Mating Area Plating Material Thickness	.38 μm[15 μin]
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	.5 A

Termination Features



Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

PCB Mounting Style	Double-Sided (Belly-to-Belly)
Connector Mounting Type	Board Mount

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Housing Color	Black
Centerline (Pitch)	.8 mm [.031 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C [-67 – 185 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | X2



Documents

Product Drawings

70 POS PT CONNECTOR, X2, XENPAK, 15 AU

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1367337-1_G.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1367337-1_G.3d_igs.zip](#)

English

Customer View Model



[ENG_CVM_CVM_1367337-1_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1773408-1 Pluggable Input/Output Solutions catalog - X2 section](#)

English

[1-1773717-7_PLUGGABLE_IO_ORG_CN](#)

English

[1-1773717-8_PLUGGABLEIO_ORG_TCN](#)

English

[1-1773717-9_HIGH_SPEED_IO_ORG_JA](#)

English

[4-1773455-2 - Quick Reference Guide Pluggable I/O Solutions](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_1367337-1_052120181246_dmtec](#)

English

[MD_1367337-1_052120181246_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English