



Relays, Contactors & Switches > Relays > Power Relays > Forced Guided Relay, Reinforced Insulate



Power Relay Type: **Force-Guided**

Coil Power Rating Class: **1000 – 1500 mW**

Coil Power Rating DC: **1200 mW**

Coil Resistance: **480 Ω**

Coil Voltage Rating: **24 VDC**

[All Forced Guided Relay, Reinforced Insulate \(78\)](#)

## Features

### Product Type Features

Power Relay Type	Force-Guided
------------------	--------------

### Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	1500 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	3000 Vrms
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms
Insulation Creepage Between Contact & Coil	5.5 mm[.217 in]
Coil Power Rating Class	1000 – 1500 mW
Coil Power Rating DC	1200 mW
Coil Resistance	480 Ω
Coil Voltage Rating	24 VDC
Contact Switching Load (Min)	10mA @ 5V
Contact Switching Voltage (Max)	400 VAC
Contact Voltage Rating	250 VAC

### Body Features

Product Weight	30 g[1.058 oz]
----------------	----------------

### Contact Features

--	--

Contact Special Features	Force Guided Contacts
Contact Arrangement	5 Form A (NO) + 1 Form B (NC)
Contact Current Class	5 – 10 A
Contact Current Rating (Max)	8 A
Contact Material	AgSnO <sub>2</sub>
Contact Number of Poles	6
Relay Terminal Type	PCB-THT

### Mechanical Attachment

Relay Mounting Type	Printed Circuit Board
---------------------	-----------------------

### Dimensions

Length Class (Mechanical)	50 – 60 mm
Height Class (Mechanical)	15 – 20 mm
Insulation Clearance Between Contact & Coil	5.5 mm [.217 in]
Width Class (Mechanical)	16 – 20 mm
Product Width	16.5 mm [.65 in]
Product Length	55 mm [2.167 in]
Product Height	16.5 mm [.65 in]

### Usage Conditions

Environmental Ambient Temperature (Max)	70 °C [158 °F]
Operating Temperature Range	-25 – 70 °C [-13 – 158 °F]

### Packaging Features

Packaging Method	Box & Tube
------------------	------------

### Other

Comment	Well suited for emergency shut-off, machine control, elevator and escalator control, light barrier control
---------	--

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022 (224)  
 Candidate List Declared Against: JUNE 2022 (224)  
 Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Wave solder capable to 260°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # 1546556-3  
 3P,STACKABLE,55 DEG,3.5MM

TE Part # 1558738-8  
 SR6-513-L024

## Also in the Series | SCHRACK SR6 A/B/C/V

Power Relays(78)

## Documents

CAD Files

Customer View Model

[ENG\\_CVM\\_1415017-1\\_SHK1.3d\\_igs.zip](#)



English

**Customer View Model**

[ENG\\_CVM\\_1415017-1\\_SHK1.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_1415017-1\\_SHK1.2d\\_dxf.zip](#)

English

**3D PDF**

3D

**3D PDF**

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1415017-1\\_G.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1415017-1\\_G.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1415017-1\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

[SR6-A-B-C-V](#)

English

[Datasheet - Force Guided Relays Schrack](#)

English

---

## Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English

---

## Agency Approvals

[UL](#)

English