

154740-1 ✓ ACTIVE


TE Internal #: 154740-1

Crimp Wire Pins, Tabs & Ferrules, Receptacle, Pin Diameter 4.44 mm [.175 in], 20 – 16 AWG Wire Size, .5 – 1.3 mm² Wire Size, 1021 – 2582 CMA Wire Size

[View on TE.com >](#)



Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Pin, Tab & Ferrule Terminal Type: **Receptacle**

Pin Diameter: **4.44 mm [.175 in]**

Accepts Wire Insulation Diameter Range: **1.5 – 2.1 mm, 2.1 mm [.059 – .083 in, .083 in]**

Wire Size: **.5 – 1.3 mm²**

Features

Product Type Features

Compatible With Discrete Wire Type **Stranded**

Configuration Features

Compatible With Wire & Cable Type **Discrete Wire**

Contact Features

Crimp Wire Pin, Tab & Ferrule Terminal Type **Receptacle**

Barrel Type **Open**

Terminal Plating Material **Unplated**

Terminal Orientation **Right Angle**

Mechanical Attachment

Wire Insulation Support **With**

Dimensions

Pin Diameter **4.44 mm [.175 in]**

Accepts Wire Insulation Diameter Range **1.5 – 2.1 mm, 2.1 mm [.059 – .083 in][.083 in]**

Wire Size **1021 – 2582 CMA**

Barrel Inside Diameter **1.27 mm, 2.54 mm [.05 in][.1 in]**



Terminal Material Thickness	.41 mm[.016 in]
-----------------------------	-----------------

Overall Product Length	9.91 mm[.39 in]
------------------------	-----------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Packaging Quantity	6000
--------------------	------

Packaging Method	Reel
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[PIN .175 DIA REC 20-16AWG PB](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_154740-1_C_c-154740-1-c.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_154740-1_C_c-154740-1-c.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_154740-1_C_c-154740-1-c.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.