



Alcoswitch

TE Internal #: 1571091-1

Rocker Switches, High Power, Panel Cutout Size .545 x 1.086 in [13.8 x 27.6 mm], Silver, Single Pole - Single Throw Configuration (Pole-Throw), On Off

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Rocker Switches



Rocker Switch Type: **High Power**

Rocker Switch Mounting Type: **Panel**

Indicator/Imprint Legend: **None**

Panel Cutout Size: **13.8 x 27.6 mm [.545 x 1.086 in]**

Switch Contact Plating Material: **Silver**

Features

Product Type Features

Product Type	Switch
Rocker Switch Type	High Power
Lamp	Without
Rocker Switch LED	Without
Actuator Type	Top
Actuator Style	Rocker

Configuration Features

Indicator/Imprint Legend	None
Panel Cutout Size	13.8 x 27.6 mm [.545 x 1.086 in]
Configuration (Pole-Throw)	Single Pole - Single Throw
Operating Function	On Off

Electrical Characteristics

Rocker Switch Voltage Rating	125 VAC
------------------------------	---------

Body Features



Beveled Frame Color	Black
---------------------	-------

Actuator Color	Black
----------------	-------

Contact Features

Terminal Tab Width	6.35 mm[.24 in]
--------------------	-----------------

Switch Contact Plating Material	Silver
---------------------------------	--------

Rocker Switch Contact Current Rating	16 A
--------------------------------------	------

Termination Features

Termination Type	Quick Connect
------------------	---------------

Mechanical Attachment

Mounting Angle	Vertical
----------------	----------

Rocker Switch Mounting Type	Panel
-----------------------------	-------

Housing Features

Process Sealed	No
----------------	----

Industry Standards

UL Listed	File No. E46765
-----------	-----------------

VDE Tested	Yes
------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
----------------------------------------	--------------------------------------------------------------------------------------------------------------------------------

Halogen Content	Not Yet Reviewed for halogen content
-----------------	--------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	----------------------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1571091-2
PRBSA1-16F-BB0BW=POWER
ROCKER



TE Part # 1571092-1
PRBSB1-16F-BR000=POWER ROCKER



TE Part # 1571094-7
PRBSD3-16F-BW000,POWER ROCKER



TE Part # 5-1571131-1
PRBSA2-16F-BBRAR=POWER
ROCKER - RoHS



TE Part # 1571091-3
PRBSA1-16F-BB0CW=POWER
ROCKER



TE Part # 1571091-9
PRBSA1-16F-BB0HW=POWER
ROCKER



TE Part # 1-1571091-1
PRBSA1-16F-BW000=POWER ROCKER



TE Part # 1571091-4
PRBSA1-16L-BB000=POWER ROCKER



TE Part # 1571092-3
PRBSB1-16F-BA000=POWER ROCKER



TE Part # 1571094-4
PRBSD3-16F-BB000,POWER ROCKER

Documents

Product Drawings

[PRBSA1-16F-BB000=POWER ROCKER](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_1571091-1_G.2d_dxf.zip](#)

English



Customer View Model

[ENG_CVM_CVM_1571091-1_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571091-1_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English