



CII

TE Internal #: 1617149-2

TO-5/.100 Grid Relays, 2 Form C, DPDT, 2 C/O, 7 VDC Input, 1 A, 12 VDC Coil Voltage, 800 Ω Coil Resistance, 180 mW Coil Power (DC), 28

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Mil-Aero Relays > TO-5/.100 Grid Relays



TO-5/.100 Grid Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**

TO-5/.100 Grid Relay Input Voltage: **7 VDC**

Coil Suppression Diode: **Without**

MOSFET Driver: **Without**

Transistor Driver: **Without**

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Relay Type	Military/Aerospace High Performance
Coil Latching	Without
Product Type	Relay
MOSFET Driver	Without

Configuration Features

Transistor Driver	Without
-------------------	---------

Electrical Characteristics

Coil Magnetic System	Non-Polarized, Monostable
Vibration	30G's, 10 – 3000Hz
Actuating System	DC
Shock	75G's, 6ms
Coil Power Measurement	Milliwatts
TO-5/.100 Grid Relay Input Voltage	7 VDC
Coil Suppression Diode	Without
Coil Voltage	12 VDC
TO-5/.100 Grid Relay Coil Resistance	800 Ω



TO-5/.100 Grid Relay Coil Power Rating (DC)	180 mW
---	--------

Coil Polarity Protection Diode	Without
--------------------------------	---------

TO-5/.100 Grid Relay Contact Switching Voltage (Max)	28
--	----

Contact Features

Contact Current Class	Low Level – 1 A
-----------------------	-----------------

Pin Configuration	.175" Diameter Mounting Pad
-------------------	-----------------------------

TO-5/.100 Grid Relay Contact Arrangement	2 Form C, DPDT, 2 C/O
--	-----------------------

TO-5/.100 Grid Relay Contact Current Rating	1 A
---	-----

Termination Features

Termination Type	PC Pins
------------------	---------

Mechanical Attachment

TO-5/.100 Grid Relay Mounting Type	Printed Circuit Board
------------------------------------	-----------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not lead free process capable
---------------------------	-------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1617031-1
HFW1201K45M = M39016/6-109M



TE Part # 2-1617031-4
HFW1201K46M = M39016/6-209M



TE Part # 7-1617529-0
FW1101G00=2020 FW RELAY



TE Part # 2-1617020-8
FW1220G06 = M5757/10-040



TE Part # 1-1617028-4
HFW1101K06 = M39016/6-129L



TE Part # 1617029-4
HFW1130F01 = M39016/6-118L



TE Part # 2-1617029-4
HFW1131F01M = M39016/6-121M



TE Part # 3-1617029-1
HFW1131K00 = HFW 1/2 SIZE RELA



TE Part # 1-1617039-2
HMS1131S04P = M39016/44-031P



TE Part # 1-1617030-9
HFW1201F00 = HFW 1/2 SIZE RELA



TE Part # 3-1617030-1
HFW1201G02P = M39016/6-216P



TE Part # 2-1617538-1
HMB1230F01M=M39016/22-019M



TE Part # 1617031-1
HFW1201K00 = HFW 1/2 SIZE RELA



TE Part # 2-1617038-1
HMB1201K01M = M39016/22-009M



TE Part # 2-1617033-5
HFW1230G01P = M39016/6-112P



TE Part # 2-1617039-5
HMS1201S109M = M39016/44-017M



Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_1617149-2_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617149-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617149-2_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec1_MGS](#)

English