



CII

TE Internal #: 1617806-3

Time Delay Relays, Fixed, 28 VDC Input, 10A@28VDC A / 115VAC A, Delay on Operate, .5 seconds Delay Time, Raised Vertical Flange Mount

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Fixed**

Time Delay Relay Input Voltage: **28 VDC**

Time Delay Relay Contact Current Rating: **10A@28VDC A, 115VAC A**

Mode of Operation: **Delay on Operate**

Delay Time: **.5 seconds**

Features

Product Type Features

Enclosure Type	Hermetic Sealed Metallic
Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

Configuration Features

Status Indicator Type	None
Multiple Timing Ranges	Without

Electrical Characteristics

Actuating System	DC
Time Delay Relay Input Voltage	28 VDC

Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Contact Base Material	Silver Cadmium Oxide
Type of Control	Fixed
Time Delay Relay Contact Current Rating	10A@28VDC A, 115VAC A
Delay Time	.5 seconds

Termination Features

Termination Type	Solder Hook Terminal
------------------	----------------------

Mechanical Attachment

Time Delay Relay Mounting Type	Raised Vertical Flange Mount
--------------------------------	------------------------------

Dimensions

Dimensions (L x W x H) (Approximate)	25.79 x 25.79 x 25.4 mm[1.015 x 1.015 x 1 in]
--------------------------------------	---

Usage Conditions

Operating Temperature Range	-55 – 125 °C
-----------------------------	--------------

Operation/Application

Mode of Operation	Delay on Operate
-------------------	------------------

Other

Repeatability (Max)	±10%
---------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[TD228-5000S=TDFO .5 SEC](#)

English

Datasheets & Catalog Pages

[High_Performance_Relays_Section5](#)

English