

165304 ✓ ACTIVE

SOLISTRAND

TE Internal #: 165304

Ring Terminals & Spade Terminals, Ring Tongue, 12 – 10 AWG
Wire Size, 4 – 6 mm² Wire Size, 10383.311 – 16511.77 CMA Wire
Size, Stud Size M8

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals



Ring & Spade Terminal Type: **Ring Tongue**

Wire Size: **10383.311 – 16511.77 CMA**

Stud Size: **M8**

Features

Product Type Features

Shape Description	RING-101
Stud Size	M8
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	180 °

Contact Features

Ring & Spade Terminal Type	Ring Tongue
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions



Wire Size	10383.311 – 16511.77 CMA
Stud Diameter	8 mm[.315 in]
Tongue Thickness	.79 mm[.031 in]
Overall Product Length	26.24 mm[1.033 in]
Barrel Inside Diameter	3.61 mm[.142 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin
Heavy Duty	No

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

SOLIS DIN 4.0-6.0 R M8

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_165304_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_165304_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_165304_H.3d_stp.zip](#)

English

165304

Ring Terminals & Spade Terminals, Ring Tongue, 12 – 10 AWG Wire Size, 4 – 6 mm²
Wire Size, 10383.311 – 16511.77 CMA Wire Size, Stud Size M8



Datasheets & Catalog Pages

DIN 46234 SOLISTRAND Terminals

English