

166053-1 ✓ ACTIVE

AMPLIMITE


TE Internal #: 166053-1

D-Sub Connector Contacts, Pin, Size 20, Brass, Gold, Crimp, 24 – 20 AWG Wire Size, .2 – .56 mm<sup>2</sup> Wire Size, Cable-to-Cable, Wire & Cable, 2 A, Signal

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connector Contacts > D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



Contact Type: **Pin**

D-Sub Contact Size: **20**

Contact Base Material: **Brass**

Contact Mating Area Plating Material: **Gold**

Termination Method to Wire & Cable: **Crimp**

[All D-Sub Connector Contacts: Pin, Brass, Signal, Size 20 \(55\)](#)

### Features

#### Product Type Features

Product Type	Contact
Grade	Standard
Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

#### Body Features

Color Code	Red
------------	-----

#### Contact Features

Pin Diameter	1 mm
Contact Mating Area Plating Thickness	.76 μm
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Type	Pin



D-Sub Contact Size	20
Contact Base Material	Brass
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	2 A

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Contact Retention Type Within Housing	Snap-In
Wire Insulation Support	With

#### Dimensions

Insulation Diameter (Max)	1.52 mm
Accepts Wire Insulation Diameter Range	1.27 – 1.52 mm [.05 – .06 in]
Wire Size	.2 – .56 mm <sup>2</sup>

#### Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

#### Operation/Application

Circuit Application	Signal
---------------------	--------

#### Packaging Features

Packaging Quantity	12500
Packaging Method	Reel

#### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 58448-3  
PRO-CRIMPER DIE



TE Part # 91503-1  
CCII AMPLIMITE 20 DF PIN SKT 28-20 ASSY



TE Part # 1579007-9  
EXTRACTION TOOL



TE Part # 58448-2  
PRO CR. ASSY AMPLIMITE IS 9357



TE Part # 2305570-1  
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 91285-1  
INSERT/EXTRACT TOOL ASSEMBLY



TE Part # 2-2151496-1  
OCEAN\_2.0\_APPLICATOR-S-055F062O



TE Part # 2-2151496-2  
OCEAN\_2.0\_APPLICATOR-S-055F062OA



TE Part # 2151496-1  
OCEAN\_2.0\_APPLICATOR-S-055F062O



TE Part # 2151496-2  
OCEAN\_2.0\_APPLICATOR-S-055F062OA



TE Part # 5-2151496-1  
OCEAN\_2.0\_APPLICATOR-S-055F062O



TE Part # 7-2151496-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-055F062O

## Documents

### Product Drawings

COSI PIN CONTACT HD20 DF; 24-20 AWG

English



### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_166053-1\\_AB.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_166053-1\\_AB.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_166053-1\\_AB.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Subminiature D Connectors for Cable Mounting](#)

English

[NECTOR\\_S\\_LINE\\_CONNECTOR\\_BROCHURE](#)

English

### Product Specifications

[Application Specification](#)

English

### Product Environmental Compliance

[MD\\_166053-1\\_09142017105\\_dmtec](#)

English

[MD\\_166053-1\\_09142017105\\_dmtec](#)

English