



TE Internal #: 170263-1

Connector Contact, Socket, Wire-to-Board / Wire-to-Wire, 30 – 26 AWG Wire Size, .05 – .15 mm² Wire Size, Tin, Strip, Wire & Cable, 2 A, Signal

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Socket**

Connector System: **Wire-to-Board, Wire-to-Wire**

Wire Size: **.05 – .15 mm²**

Contact Mating Area Plating Material: **Tin**

Features

Product Type Features

Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	750 VAC
Insulation Resistance	500 MΩ
Operating Voltage	250 VAC

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.8 μm
Contact Base Material	Brass
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	2 A

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Dimensions

Accepts Wire Insulation Diameter Range	1 – 1.4 mm[.039 – .055 in]
--	----------------------------



Wire Size	.05 – .15 mm ²
-----------	---------------------------

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	10000
--------------------	-------

Packaging Method	Strip
------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 171822-8 EIS REC. HSG 8P-NATURAL</p>	 <p>TE Part # 171822-6 EIS REC. HSG 6P-NATURAL</p>	 <p>TE Part # 171822-7 EIS REC. HSG 7P-NATURAL</p>	 <p>TE Part # 1-171822-2 EIS REC. HSG 12P-NATURAL</p>
 <p>TE Part # 171822-5 EIS REC. HSG 5P-NATURAL</p>	 <p>TE Part # 171822-9 EIS REC. HSG 9P-NATURAL</p>	 <p>TE Part # 171822-3 EIS REC. HSG 3P-NATURAL</p>	 <p>TE Part # 171822-2 EIS REC. HSG 2P-NATURAL</p>
 <p>TE Part # 1-171822-0 EIS REC. HSG 10P-NATURAL</p>	 <p>TE Part # 171822-4 EIS REC. HSG 4P-NATURAL</p>	 <p>TE Part # 172486-2 2P REC HSG CRIMP EI SER</p>	 <p>TE Part # 2-171822-3 EIS REC. HSG 3P-BLACK</p>
 <p>TE Part # 2-171822-4 EIS REC. HSG 4P-BLACK</p>	 <p>TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp</p>	 <p>TE Part # 4-171822-5 EIS REC. HSG 5P-BLUE</p>	 <p>TE Part # 91556-1 CCII AMP EI SERIES 26-20 ASSY</p>
 <p>TE Part # 4-171822-4 EIS REC. HSG 4P-BLUE</p>	 <p>TE Part # 172486-3 3P REC HSG CRIMP EI SER</p>	 <p>TE Part # 4-171822-8 E.I.SERIES CONN REC 8P</p>	 <p>TE Part # 4-172486-2 2P REC HSG CRIMP EI SERBLUE</p>

Documents

[Product Drawings](#)
[EIS CONTACT](#)



English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_170263-1_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_170263-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_170263-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773972-5_EIS_Connectors_Brochure](#)

English

Product Specifications

[Crimping of AMP EI Series Connector Contacts](#)

Japanese

[Application Specification](#)

Japanese

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[AMP "EI" Series Connector](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

Agency Approvals

[Agency Approval Document](#)

English