

171370-4 ✓ ACTIVE


TE Internal #: 171370-4

Magnet Wire Terminals, Crimp, Length 31.6 mm [1.24 in], Bag,
Straight, -40 – 266 °F [-40 – 130 °C]

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Termination Method to Wire & Cable: **Crimp**

Overall Product Length: **31.6 mm [1.24 in]**

Packaging Method: **Bag**

Terminal Orientation: **Straight**

Sealable: **No**

Features

Product Type Features

Insulated	No
Sealable	No

Contact Features

Terminal Orientation	Straight
----------------------	----------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Dimensions

Overall Product Length	31.6 mm[1.24 in]
------------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 171370-3 CLUSTER BLOCK HSG PBT</p>	 <p>TE Part # 1-171370-1 2.3 DIA CLUSTER BLOCK HSG</p>	 <p>TE Part # 1-171370-2 2.3DIA CLUSTER BLOCK</p>	 <p>TE Part # 171370-5 CLUSTER BLOCK HSG PBT</p>
 <p>TE Part # 2232326-1 CLUSTER BLOCK HSG .090 DIA</p>	 <p>TE Part # 1-2005820-1 CLUSTER BLOCK 3P CLIP HSG</p>	 <p>TE Part # 171370-6 CLUSTER BLOCK HSG 66 0023</p>	 <p>TE Part # 171370-7 CLUSTER BLOCK HSG LCP</p>



Documents

Product Drawings

CLUSTER BLOCK HSG GWT

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_171370-4_R.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_171370-4_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_171370-4_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

[MD_171370-4_03162018941_dmtec](#)

English

[MD_171370-4_03162018941_dmtec](#)

English