

173974-7 ✓ ACTIVE



Positive Lock | Positive Lock 187

TE Internal #: 173974-7

Crimp Terminal Housings, Receptacle, Receptacle, 1 Position,  
Straight, UL 94V-0, Red, Nylon, Contact Mating Retention, Positive  
Lock 187

[View on TE.com >](#)

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**

Housing Type: **Receptacle**

Number of Positions: **1**

Terminal Orientation: **Straight**

UL Flammability Rating: **UL 94V-0**

## Features

### Product Type Features

Terminates To	Wire & Cable
Product Type	Terminal Housing
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Housing Type	Receptacle
Insulated	No

### Configuration Features

Number of Positions	1
---------------------	---

### Body Features

Primary Product Color	Red
-----------------------	-----

### Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

### Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	Nylon
------------------	-------

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	1000
--------------------	------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # 170330-2  
PL 187 RECEPTACLE 24-20 AWG  
NPPHBZ

TE Part # 170332-1  
PL 187 RECEPTACLE 18-14 AWG  
PTPBR

TE Part # 170324-2  
PL 187 RECEPTACLE 24-20 AWG 0.3  
NPCU

TE Part # 170326-5  
187 PL MKII REC. 18-14AWG PTPB

TE Part # 170326-1  
187 PL MKII REC. 18-14AWG PTBR

TE Part # 170325-5  
187 PL MKII REC. 20-16AWG PTBR

TE Part # 170325-1  
187 PL MKII REC. 20-16AWG PTBR

TE Part # 170324-1  
187 PL MKII REC. 24-20AWG PTBR

TE Part # 170331-1  
PL MKII 187 REC 20-16AWG PTBR LP

TE Part # 170330-1  
PL MKII 187 REC 24-20AWG PTBR LP

## Also in the Series | Positive Lock 187

Crimp Terminal Housings(87)

Insertion & Extraction Tools(2)

Insulation Boots & Sleeves(7)

Quick Disconnects(56)

## Documents

### Product Drawings

[PL 187 \(4.8 MM\) HOUSING RECEPTACLE](#)



English

---

**CAD Files**

**3D PDF**

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_173974-7\\_P.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_173974-7\\_P.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_173974-7\\_P.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

**Positive Lock Receptacles**

English

---

**Product Specifications**

**187 SERIES POSITIVE LOCK MARK-II CONNECTOR**

Japanese

**Product Specification**

Japanese

**Product Specification**

English

**JAPANESE**

English

---

**Product Environmental Compliance**

[MD\\_173974-7\\_04032015235\\_dmtec](#)

English

[MD\\_173974-7\\_04032015235\\_dmtec](#)

English