

176271-4 ✓ ACTIVE

AMP Universal Power


TE Internal #: 176271-4

Rectangular Power Connectors, Housing, Plug, Wire-to-Wire, 2 Position, 3.96 mm [.156 in] Centerline, Wire & Cable, UL 94V-0, AMP Universal Power

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **3.96 mm [.156 in]**

### Features

#### Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

#### Configuration Features

Number of Positions	2
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

#### Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

#### Contact Features

Contact Layout	Inline
----------------	--------



Contact Retention Within Housing	Without
----------------------------------	---------

Contact Type	Receptacle
--------------	------------

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Strain Relief	Without
---------------	---------

Mating Alignment Type	Polarization
-----------------------	--------------

Mating Alignment	Without
------------------	---------

Panel Mount Feature	Without
---------------------	---------

PCB Mount Retention	Without
---------------------	---------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Mating Retention	With
------------------	------

Mating Retention Type	Latch
-----------------------	-------

### Housing Features

Centerline (Pitch)	3.96 mm [.156 in]
--------------------	-------------------

Housing Color	Yellow
---------------	--------

Housing Material	PA 6/6
------------------	--------

### Dimensions

Height	10.05 mm
--------	----------

Length	9.06 mm
--------	---------

### Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

### Packaging Features

Packaging Method	Bag
------------------	-----

Packaging Quantity	1000
--------------------	------

### Other



For Use With	Cap Housing
--------------	-------------

### Product Compliance





[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 175156-2 U/P REC CONT L/P</p>	 <p>TE Part # 175155-1 UNIV POWER REC CONT L/P</p>	 <p>TE Part # 9-176975-1 AMP UNIVERSAL POWER PLG 2P PCB</p>	 <p>TE Part # 176282-4 AMP UNIVERSAL POWER CAP 2P</p>
--	---	--	--

			
TE Part # 176282-1 AMP UNIVERSAL POWER CAP 2P	TE Part # 175151-1 AMP UNIVERSAL POWER REC CONT.	TE Part # 175152-1 UNIVERSAL POWER REC	TE Part # 175152-2 AMP UNIVE. POWER CONN REC CONT
			
TE Part # 175151-2 AMP UNIVE. POWER CONN REC CONT	TE Part # 175155-2 U/P REC CONT L/P	TE Part # 175156-1 UNIV POWER REC CONT L/P	TE Part # 176282-2 AMP UNIVERSAL POWER CAP 2P
			
TE Part # 178495-9 UP 3.96 2P DIP HDR BLACK	TE Part # 176292-1 UNIV POWER CAP HSG 2P P/MOUNT	TE Part # 178495-1 UP 3.96 2P DIP HDR NAT	TE Part # 176282-6 AMP UNIVERSAL POWER CAP 2P
			
TE Part # 175151-5 AMP UNIVERSAL POWER CONN.REC C	TE Part # 1-176975-1 AMP UNIVERSAL POWER PLG 2P PCB	TE Part # 1-176975-9 UNIV POWER HDR ASSY 2P BLACK	TE Part # 176975-2 UNIV POWER HDR ASSY 2P RED

Also in the Series | AMP Universal Power

			
Connector Contacts(1)	Insertion & Extraction Tools(1)	Power Contacts(21)	Rectangular Power Connectors(177)

Documents



### Product Drawings

#### AMP UNIVERSAL POWER PLUG 2P

English

---

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_176271-4\\_H.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_176271-4\\_H.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_176271-4\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

#### Crimping of Universal Power Contact

English

#### Product Specification

Japanese

#### AMP Universal Power Connector

Japanese

---

### Product Environmental Compliance

[MD\\_176271-4\\_053120182151\\_dmtec](#)

English

[MD\\_176271-4\\_053120182151\\_dmtec](#)

English

---

### Instruction Sheets

#### AMP UNIVERSAL POWER CONNECTOR SERIES

English

#### Instruction Sheet (non U.S.)

English

---

### Agency Approvals

#### UL Report

English