

178482-1 ✓ ACTIVE

AMP Universal Power


TE Internal #: 178482-1

Rectangular Power Connectors, Housing, Plug, Wire-to-Wire, 5 Position, 3.96 mm [.156 in] Centerline, Wire & Cable, UL 94V-0, AMP Universal Power

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **5**

Centerline (Pitch): **3.96 mm [.156 in]**

### Features

#### Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

#### Configuration Features

Number of Positions	5
Number of Rows	1

#### Electrical Characteristics

Operating Voltage	300 VAC
Insulation Resistance	1000 MΩ

#### Contact Features

Contact Layout	Inline
Contact Base Material	Copper Alloy



Contact Current Rating (Max)	7 A
Contact Retention Within Housing	Without
Contact Type	Receptacle

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Panel Mount
Mating Retention	With
Mating Retention Type	Latch

#### Housing Features

Centerline (Pitch)	3.96 mm [.156 in]
Housing Color	Natural
Housing Material	Nylon 6/6

#### Dimensions

Height	9.7 mm [.38 in]
Length	20.94 mm [.67 in]

#### Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

#### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

#### Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

#### Packaging Features

Packaging Method	Bag
Packaging Quantity	500



Other

For Use With	Header Assembly
--------------	-----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 175156-2 U/P REC CONT L/P</p>	 <p>TE Part # 175155-1 UNIV POWER REC CONT L/P</p>	 <p>TE Part # 175151-1 AMP UNIVERSAL POWER REC CONT.</p>	 <p>TE Part # 175152-1 UNIVERSAL POWER REC</p>
------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------




TE Part # 175152-2  
AMP UNIVE. POWER CONN REC  
CONT



TE Part # 175151-2  
AMP UNIVE. POWER CONN REC  
CONT



TE Part # 175155-2  
U/P REC CONT L/P



TE Part # 175156-1  
UNIV POWER REC CONT L/P



TE Part # 2-178488-1  
UP 7.92 3P TAB HDR NAT TYPE 1




TE Part # 178488-1  
UP 3.96 5P TAB HDR NAT TYPE 1



TE Part # 178498-1  
UP 3.96 5P TAB HDR NAT TYPE 1



TE Part # 175151-5  
AMP UNIVERSAL POWER CONN.REC  
C



TE Part # 178479-1  
AMP UP CAP HSG F/H 5P NATURAL



TE Part # 3-178498-1  
UP 7.92 3P TAB HDR NATL TYPE 1



TE Part # 4-178488-1  
AMP U/P SGL ROW HDR ASSY V 4P



TE Part # 175151-4  
UNIVESAL POWER REC CONT #26-22



TE Part # 175152-3  
UNIV POWER REC CONT



TE Part # 175152-4  
UNIVESAL POWER REC CONT #20-16




TE Part # 2-178488-4  
UP 7.92 3P TAB HDR YELLO TYP 1




TE Part # 3-178488-1  
UP 7.92 3P TAB HDR NAY TYPE 2


Also in the Series | AMP Universal Power




Connector Contacts(1)



Insertion & Extraction Tools(1)



Power Contacts(21)



Rectangular Power Connectors(177)

Documents



### Product Drawings

#### [UP 3.96 5P PLUG HSG NATRL](#)

English

#### [UP 3.96 5P PLUG HSG NATRL](#)

English

---

### CAD Files

#### [3D PDF](#)

3D

#### [Customer View Model](#)

[ENG\\_CVM\\_CVM\\_178482-1\\_O.2d\\_dxf.zip](#)

English

#### [Customer View Model](#)

[ENG\\_CVM\\_CVM\\_178482-1\\_O.3d\\_igs.zip](#)

English

#### [Customer View Model](#)

[ENG\\_CVM\\_CVM\\_178482-1\\_O.3d\\_stp.zip](#)

English

#### [3D PDF](#)

English

#### [Customer View Model](#)

[ENG\\_CVM\\_178482-1\\_A.2d\\_dxf.zip](#)

English

#### [Customer View Model](#)

[ENG\\_CVM\\_178482-1\\_A.3d\\_igs.zip](#)

English

#### [Customer View Model](#)

[ENG\\_CVM\\_178482-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

#### [Crimping of Universal Power Contact](#)

English

#### [Product Specification](#)

Japanese

#### [AMP Universal Power Connector](#)

Japanese

---

### Product Environmental Compliance

#### [TE Material Declaration](#)

English

---

### Instruction Sheets

#### [AMP UNIVERSAL POWER CONNECTOR SERIES](#)



English

[Instruction Sheet \(non U.S.\)](#)

English

---

[Agency Approvals](#)

[UL Report](#)

English