




[Alcoswitch](#) | [Alcoswitch DIP](#), [Alcoswitch DIP Shunt](#)

TE Internal #: 1825190-3

DIP & SIP Switches, Shunt, Tin, Black Housing, High Temperature Nylon, 4 Switch, DIP, 2 A, Alcoswitch DIP

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > DIP & SIP Switches



DIP & SIP Switch Product Type: **Shunt**

DIP & SIP Switch Contact Mating Area Plating Material: **Tin**

DIP & SIP Switch Housing Color: **Black**

DIP & SIP Switch Housing Material: **High Temperature Nylon**

Auto-Insertable: **No**

Features

Product Type Features

DIP & SIP Switch Product Type	Shunt
Sealed DIP & SIP Switch	No
DIP & SIP Switch Type	DIP

Configuration Features

Number of Positions	4
Number of Switches	4
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

DIP & SIP Switch Voltage Rating	500 VDC
---------------------------------	---------

Contact Features

Solder Tail Contact Plating	Tin
Shunt Type	DIP
DIP & SIP Switch Contact Mating Area Plating Material	Tin
Auto-Insertable	No



DIP & SIP Switch Contact Current Rating	2 A
---	-----

Contact Base Material	Copper Alloy
-----------------------	--------------

Termination Features

Termination Post Length	3.8 mm[.15 in]
-------------------------	----------------

Mechanical Attachment

Mounting Angle	Right Angle
----------------	-------------

DIP & SIP Switch Mounting Type	Through Hole
--------------------------------	--------------

Housing Features

DIP & SIP Switch Housing Color	Black
--------------------------------	-------

DIP & SIP Switch Housing Material	High Temperature Nylon
-----------------------------------	------------------------

DIP & SIP Switch Centerline	2.54 mm[.1 in]
-----------------------------	----------------

Dimensions

Height	2 mm[.079 in]
--------	---------------

Length	10.16 mm[.399 in]
--------	-------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Packaging Quantity	500
--------------------	-----

Other

Comment	Soldering in "off" position only
---------	----------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2022 (224)</p> <p>Candidate List Declared Against: JUNE 2022 (224)</p> <p>SVHC > Threshold:</p> <p>Pb (.34% in Component Part)</p> <p><small>Article Safe Usage Statements:</small></p>
--	---



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | Alcoswitch DIP



Also in the Series | Alcoswitch DIP Shunt



DIP & SIP Switches(4)

Documents

Product Drawings

[DIP Shunt,4 pos](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1825190-3_C1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825190-3_C1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825190-3_C1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_1825190-3_04132012725](#)

English

[MD_1825190-3_04132012725](#)

English