

1969567-8 ✓ ACTIVE

Economy Power 2.5

TE Internal #: 1969567-8

Housing, Plug, Wire-to-Wire, 8 Position, 2.5 mm [.098 in] Centerline,
Crimp, 2 Row, Natural, Mating Retention, Wire & Cable, Economy
Power 2.5

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **8**

Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

| | |
|-----------------------------------|--------------|
| Connector Product Type | Housing |
| Connector & Housing Type | Plug |
| Connector System | Wire-to-Wire |
| Sealable | No |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 8 |
| Number of Rows | 2 |

Electrical Characteristics

| | |
|-------------------|---------|
| Operating Voltage | 250 VAC |
|-------------------|---------|

Contact Features

| | |
|------------------------------|--------|
| Contact Type | Socket |
| Contact Current Rating (Max) | 7.5 A |



Termination Features

| | |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

| | |
|-------------------------|----------------------------|
| Strain Relief | Without |
| Panel Mount Feature | Without |
| PCB Mount Retention | Without |
| Mating Retention Type | Latch |
| Mating Retention | With |
| Connector Mounting Type | Cable Mount (Free-Hanging) |

Housing Features

| | |
|-----------------------------|------------------|
| Housing Entry Configuration | Both Ends Closed |
| Housing Material | Nylon - GF |
| Centerline (Pitch) | 2.5 mm [.098 in] |
| Housing Color | Natural |

Dimensions

| | |
|--|-------------------------------|
| Connector Length | 11.04 mm [.435 in] |
| Connector Height | 8.3 mm [.326 in] |
| Connector Width | 12.32 mm [.485 in] |
| Accepts Wire Insulation Diameter Range | 1.3 – 1.7 mm [.051 – .067 in] |
| Wire Size | .13 – .33 mm ² |
| Row-to-Row Spacing | 2.5 mm [.09 in] |

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -25 – 105 °C [-13 – 221 °F] |
|-----------------------------|-----------------------------|

Operation/Application

| | |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Industry Standards

| | |
|------------------------|-----------|
| Glow Wire Rating | Glow Wire |
| UL Flammability Rating | UL 94V-0 |

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 3200 |
| Packaging Method | Bag |



Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|--|---|--|--|
|  <p>TE Part # 1969540-8 HOUSING, PLUG, 8P, DUAL ROW, EP2.5</p> |  <p>TE Part # 1-1969567-4 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |  <p>TE Part # 1-1969567-2 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |  <p>TE Part # 3-1969567-0 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |
|  <p>TE Part # 2-1969567-8 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |  <p>TE Part # 1-1969567-6 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |  <p>TE Part # 1-1969567-8 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |  <p>TE Part # 2-1969567-2 HOUSING, PLUG, GWT, DUAL ROW, EP2.5</p> |



TE Part # 2-1969567-6
HOUSING, PLUG, GWT, DUAL ROW,
EP2.5



TE Part # 2-1969567-0
HOUSING, PLUG, GWT, DUAL ROW,
EP2.5




TE Part # 2-1969567-4
HOUSING, PLUG, GWT, DUAL ROW,
EP2.5


Also in the Series | Economy Power 2.5



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(408)



PCB Latches, Locks & Retainers(49)



Rectangular Power Connectors(43)



Wire-to-Board Connector Assemblies
& Housings(311)



Wire-to-Board Connector Contacts(6)

Documents

Product Drawings

HOUSING, PLUG, GWT, DUAL ROW, EP2.5

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1969567-8_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969567-8_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969567-8_B.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[7-1773461-6_EP2.5_Connector_Series](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_1969567-8_03232018646_dmtec](#)

English

[MD_1969567-8_03232018646_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English