




XFP

TE Internal #: 1888810-2

XFP, Accessory, Data Rate (Max) 10 Gb/s, XFP

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > XFP



Pluggable I/O Product Type: **Accessory**

Data Rate (Max): **10 Gb/s**

**Features**

**Product Type Features**

Form Factor	XFP
Pluggable I/O Accessory Type	Dust & EMI Cover
Pluggable I/O Product Type	Accessory

**Electrical Characteristics**

Data Rate (Max)	10 Gb/s
-----------------	---------

**Body Features**

Primary Product Material	Zinc Alloy
--------------------------	------------

**Operation/Application**

For Use With Pluggable I/O Products	XFP Cage
-------------------------------------	----------

**Packaging Features**

Packaging Method	Carton
------------------	--------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-X29-C1171XN  
XFP Cage Assemblies and Kits



TE Part # CAT-Q17-AC229  
QSFP Heat Sink Clips



TE Part # 2143330-1  
1X6 QSFP Kit Assy Bhnd Bzl,PCI



TE Part # 2170705-7  
CAGE ASSY, QSFP28 1X1, SPRING, HS, LP



TE Part # 2170806-5  
CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS



TE Part # 2170752-2  
CAGE ASSEMBLY, QSFP28 1X1, GASKET




TE Part # 2-2170747-2  
CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP



TE Part # 2170704-2  
CAGE ASSY, QSFP28 1X1, SPRING, HS



## Also in the Series | XFP



## Documents

### Product Drawings

EMI/Dust Cover,XFP And QSFP

English

### CAD Files

Customer View Model

ENG\_CVM\_CVM\_1888810-2\_A.2d\_dxf.zip

English



### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1888810-2\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1888810-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1773408-1 Pluggable Input/Output Solutions catalog - QSFP section](#)

English

[1773408-1 Pluggable Input/Output Solutions catalog - XFP section](#)

English

[Quad Small Form-factor Pluggable \(QSFP\) Products Datasheet 6-1773447-7](#)

English

### Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

[Application Specification](#)

English

### Product Environmental Compliance

[MD\\_1888810-2\\_080220181217\\_dmtec](#)

English

[MD\\_1888810-2\\_080220181217\\_dmtec](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English