



Connectors > Modular Jacks & Plugs > Modular Jack & Plug Accessories > Circular Ethernet Hardware



Modular Jacks & Plugs Accessory Type: **Frame Kit (Push Pull)**

Circuit Application: **Signal**

## Features

### Product Type Features

Frame Kit Type	Frame Kit Only, Push-Pull
Modular Jacks & Plugs Accessory Type	Frame Kit (Push Pull)

### Configuration Features

Wiring Pattern	RJ45
----------------	------

### Body Features

Seal Material	EPDM
---------------	------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

IP Rating	IP65/67
-----------	---------

### Packaging Features

Packaging Quantity	1
Packaging Method	Bag

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: DEC 2014 (161) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



TE Part # 1987004-1  
RJ45 PLUG, PUSH-PULL, ASSY, C AT5, SHIELDED



TE Part # 1987004-2  
RJ45 PLUG, PUSH-PULL, ASSY, C AT5, SHIELDED




TE Part # 1987978-1  
SAEL CAP FOR PUSH-PULL

Also in the Series | [Industrial Ethernet Accessories](#)



Circular Ethernet Hardware(4)



Data Connectivity Headers(1)



Data Connectivity Housings(1)



Modular Jack &amp; Plug Caps &amp; Covers(3)



RJ45 Connectors(3)

## Documents

### Product Drawings

#### [ASSY, IP67 PUSH-PULL FRAME](#)

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1987307-1\\_A1.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1987307-1\\_A1.3d\\_igs.zip](#)

English

### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1987307-1\\_A1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Agency Approvals

#### [UL Report](#)

English