

1SNA163313R2400 ✓ ACTIVE

ENTRELEC | ENTRELEC SNK


TE Internal #: 1SNA163313R2400

Terminal Block & Strip Conducting Accessories, Jumper Bar, 10 Pole, Black, Product Spacing .31 in [8 mm], Power, ENTRELEC SNK

[View on TE.com >](#)



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Jumper Bar**

Number of Poles: **10**

Primary Product Color: **Black**

Product Spacing: **8 mm [.31 in]**

Contact Current Rating (Max): **50 A**

Features

Product Type Features

Conducting Accessory Type	Jumper Bar
---------------------------	------------

Configuration Features

Number of Poles	10
-----------------	----

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Current Rating (Max)	50 A
------------------------------	------

Dimensions

Product Spacing	8 mm [.31 in]
-----------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 110 °C [-67 – 230 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1SNK508011R0000 ZS10-R1</p>	 <p>TE Part # 1SNK508151R0000 ZS10-PE-R1</p>	 <p>TE Part # 1SNK508310R0000 ZS10-ST</p>	 <p>TE Part # 1SNA105004R2200 M6/8</p>
 <p>TE Part # 1SNA105055R2400 M6/8.SNB</p>	 <p>TE Part # 1SNA105118R2000 M6/8</p>	 <p>TE Part # 1SNA105128R2200 M6/8.1</p>	 <p>TE Part # 1SNA115118R1100 M6/8</p>



Also in the Series | **ENTRELEC SNK**



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1SNA163313R2400_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SNA163313R2400_A.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1SNA163313R2400_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Catalogue - ENTRELEC terminal-blocks-sna-series](#)

English

[PC8-10](#)

English

[ENTRELEC Terminal Block - Master Catalog](#)

English

[SNK SERIES TERMINAL BLOCKS](#)

English

[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)