




Connectors > RF Coax Connectors > Coax Terminators



Impedance: 75 Ω

Circuit Application: **Signal**

Operating Temperature Range: -65 – 165 °C [-85 – 329 °F]

Features

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Body Plating Material	Silver
Body Material	Brass

Contact Features

RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 165 °C [-85 – 329 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method

Box & Tray, Tray

Other

Grade

Professional

Product Compliance[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Not Yet Reviewed

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: DEC 2014 (161)
 SVHC > Threshold:
 Not Yet Reviewed

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents**Product Drawings**[BNC Plg Term 75Ohm Silver Pltd](#)

English

CAD Files[3D PDF](#)

3D

Customer View Model[ENG_CVM_CVM_1-1337470-0_D.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1-1337470-0_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1337470-0_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.