



[Axicom](#) | [Axicom P1 Signal Relay](#)

TE Internal #: 1-1393774-0

Power Relays, Standard, Monostable, DC, 72 mW Coil Power Rating

DC, 3100 Ω Coil Resistance, 15 VDC Coil Voltage, 1 Form C (CO),

Axicom P1 Signal Relay

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Standard**

Coil Magnetic System: **Monostable, DC**

Coil Power Rating DC: **72 mW**

Coil Resistance: **3100 Ω**

Coil Voltage Rating: **15 VDC**

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Coil Magnetic System	Monostable, DC
Coil Power Rating DC	72 mW
Coil Resistance	3100 Ω
Coil Voltage Rating	15 VDC
Contact Switching Load (Min)	10mA @ .02V
Contact Switching Voltage (Max)	125 VDC
Contact Voltage Rating	125 VDC

Contact Features

Contact Arrangement	1 Form C (CO)
Contact Current Class	1 A
Contact Current Rating (Max)	1 A
Contact Material	PdNi+Au
Contact Number of Poles	1
Relay Terminal Type	PCB-THT

Mechanical Attachment

Relay Mounting Type	Through Hole
---------------------	--------------



Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | [Axicom P1 Signal Relay](#)



Power Relays(8)



Signal Relays(25)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1393774-0_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1393774-0_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1393774-0_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English

Product Specification

English