




Buchanan | Buchanan 3 Series

TE Internal #: 1-1546119-5

Barrier Strips, Tri-Barrier, Printed Circuit, Wire-to-Board, 10 Position, 6.35 mm [.25 in] Centerline, 1 Row, 300 V, Buchanan 3 Series

[View on TE.com >](#)

Connectors > Terminal Blocks & Strips > Barrier Strips



Barrier Strip Style: **Tri-Barrier**

Bottom Termination Type: **Printed Circuit**

Connector System: **Wire-to-Board**

Number of Positions: **10**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Product Type	Barrier Strip
Block Style	Open Bottom with Standoffs
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Levels	1
Number of Positions	10
Number of Rows	1

Electrical Characteristics

Current Rating (Max)	10 A
Voltage Rating	300 V

Body Features

Color	Black
Barrier Strip Style	Tri-Barrier

Contact Features

Terminal Material	Copper Alloy
Terminal Plating Finish	Bright
Terminal Plating Material	Tin



Contact Current Rating (Max)	10 A
------------------------------	------

Termination Features

Bottom Termination Type	Printed Circuit
-------------------------	-----------------

Mechanical Attachment

Mounting Angle	Right Angle
----------------	-------------

Screw Head Type	Wire Clamp Combo Head
-----------------	-----------------------

Top Termination Type	Wire Clamp Combo Head
----------------------	-----------------------

Mounting Insert	Without
-----------------	---------

Screw Plating Material	Zinc
------------------------	------

Screw Plating Finish	Bright
----------------------	--------

Screw Material	Steel
----------------	-------

Mounting Options	None
------------------	------

Mounting Ears	Without
---------------	---------

Screw Size	M3
------------	----

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	Thermoplastic
------------------	---------------

Centerline (Pitch)	6.35 mm [.25 in]
--------------------	------------------

Dimensions

Length	64.7 mm [2.55 in]
--------	-------------------

Wire Size	.05 – 1.4 mm ²
-----------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	Other options available upon request, consult our Product Information Center.
---------	---

Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Buchanan 3 Series](#)



Barrier Strips(61)

Documents

Product Drawings

[3PCR-10-006=3PCR ASSY](#)

English

Datasheets & Catalog Pages

[1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE](#)

English