



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Secondary Housing Lock**

Features

Product Type Features

Insertion & Extraction Tool Type	Secondary Housing Lock
----------------------------------	------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (.91% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-M4595-T273
MCON, RECEPTACLE AND TAB



TE Part # 1-2298627-1
24POS, HYBRID, TAB HSG ASSY,
UNSLD, COD A



TE Part # 2298622-1
24POS, HYBRID, REC HSG ASSY,
UNSLD, COD A



TE Part # 2298627-1
24POS, HYBRID, TAB HSG ASSY,
UNSLD, COD A

TE Part # 1-1418845-1
AMP MCP 1.2-CB-LP

TE Part # 1-1418845-2
AMP MCP 1.2-CB-LP

TE Part # 1-1418845-3
AMP MCP 1.2-CB-LP

TE Part # 1-1418848-1
AMP MCP 1.2-CB-LP

TE Part # 1-1418848-2
AMP MCP 1.2-CB-LP

TE Part # 1-1418848-3
AMP MCP 1.2-CB-LP

TE Part # 1-1418851-1
AMP MCP 1.2-CB-LP


TE Part # 1-1418851-2
AMP MCP 1.2-CB-LP

TE Part # 1-1418851-3
AMP MCP 1.2-CB-LP


TE Part # 1-1534063-1
AMP MCP 1.2-CB-LP

TE Part # 1-1534063-2
AMP MCP 1.2-CB-LP

TE Part # 1-1534063-3
AMP MCP 1.2-CB-LP



Also in the Series | **MCON Interconnection System**



Documents

Product Drawings

EXTRACTION TOOL

English

Datasheets & Catalog Pages

CRIMPING TERMINALS

English

CRIMPING WHERE FORM MEETS FUNCTION

English