




TE Internal #: 1-179322-2

Connector Contact, Pin, Wire-to-Board, 12 mm [.472 in] Centerline,  
24 – 20 AWG Wire Size, 394.71 – 986.76 CMA Wire Size, .2 – .5 mm<sup>2</sup>  
Wire Size, Tin

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Pin**

Connector System: **Wire-to-Board**

Centerline (Pitch): **12 mm [.472 in]**

Wire Size: **394.71 – 986.76 CMA**

### Features

#### Product Type Features

Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

#### Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

#### Contact Features

Mating Tab Width	3 mm[.118 in]
Mating Tab Thickness	.65 mm[.025 in]
Contact Underplating Material Thickness	.8 μm[31.5 μin]
Contact Mating Area Plating Material Thickness	.38 μm[15 μin]
Contact Length	29.2 mm[1.15 in]
Contact Base Material	Copper Alloy
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	7 A

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------



**Housing Features**

Centerline (Pitch)	12 mm [.472 in]
--------------------	-----------------

**Dimensions**

Accepts Wire Insulation Diameter Range	1.4 – 2.6 mm [.055 – .102 in]
Wire Size	.2 – .5 mm <sup>2</sup>

**Usage Conditions**

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

**Operation/Application**

Compatible With Wire Base Material	Copper
Circuit Application	Power & Signal

**Packaging Features**

Packaging Quantity	4500
Packaging Method	Reel

**Other**

Comment	Housing PN: X-179325-X, X-179318-X, X-179388-X
---------	--

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # CAT-AM7053-D797P  
Mini CT Drawer Connector Assemblies



TE Part # 1-292183-2  
PLUG ASS'Y OF HYB DRAWER 18P



TE Part # 292182-8  
PLUG ASS'Y OF HYB DRAWER 12P



TE Part # 2305570-1  
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 2-292181-8  
PLUG ASS'Y OF HYB DRAWER 32P



TE Part # 2-292181-0  
PLUG ASS'Y OF HYB DRAWER 24P



TE Part # 7-2151124-1  
OCEAN-2.0-APPLICATOR-S-062F120F



TE Part # 7-2151124-2  
OCEAN-2.0-APPLICATOR-S-062F120F



TE Part # 2-2151124-1  
OCEAN-2.0-APPLICATOR-S-062F120F



TE Part # 2-2151124-2  
OCEAN-2.0-APPLICATOR-S-062F120F



TE Part # 2151124-1  
OCEAN-2.0-APPLICATOR-S-062F120F



TE Part # 2151124-2  
OCEAN-2.0-APPLICATOR-S-062F120F



TE Part # 7-2151124-7  
OC-062F120F-CRIMPTOOLINGKIT

## Documents

### Product Drawings



## HYBRID MINI DRAWER TAB CONT.

English

---

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-179322-2\\_K2.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-179322-2\\_K2.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-179322-2\\_K2.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[POWER\\_CONNECTORS\\_CATALOG\\_SEC02\\_CABLE\\_MOUNTED](#)

English

[Low Power Drawer Connectors QRG](#)

English

---

### Product Specifications

#### Application Specification

English

[Crimping Hybrid Mini Drawer Connector Power Line Contact](#)

English

---

### Product Environmental Compliance

#### TE Material Declaration

English