

1-2213395-1 ✓ ACTIVE


TE Internal #: 1-2213395-1

Standard Circular Connectors, Cable-to-Cable, 3 Position, 0 Power Positions, 0 Signal Positions, Plug, Pin

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Number of Positions: **3**

Number of Power Positions: **0**

Number of Signal Positions: **0**

Circular Connector Type: **Plug**

Features

Product Type Features

Prewired	No
Connector System	Cable-to-Cable
Circular Connector Type	Plug

Configuration Features

Keying & Polarized Position Locations	Normal
Keying	A
Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	0

Contact Features

Circular Connector Contact Type	Pin
---------------------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUN 2018 (191)

SVHC > Threshold:

Not Yet Reviewed

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

NECTOR M FI PIN ASSEMBLY, FREE HANG

English

CAD Files

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

1-2213395-1

Standard Circular Connectors, Cable-to-Cable, 3 Position, 0 Power Positions, 0 Signal Positions, Plug, Pin

