

1-332056-0 ✓ ACTIVE

TE Internal #: 1-332056-0


RF Connector Ferrules, RG 174 / RG 188A / Belden 9221, Ferrule

Inside Diameter 2.84 mm [.112 in], Copper, Tin Plating

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Coax Accessories > Ferrules



Connector & Contact Terminates To: **Wire & Cable**

Compatible With RF Cable Type: **Belden 9221, RG 161, RG 174, RG 179, RG 179A, RG 179B, RG 187, RG 187A, RG 188, RG 188A, RG 316**

Ferrule Inside Diameter: **2.84 mm [.112 in]**

Ferrule Material: **Copper**

Ferrule Plating Material: **Tin**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Compatible With RF Cable Type	Belden 9221, RG 161, RG 174, RG 179, RG 179A, RG 179B, RG 187, RG 187A, RG 188, RG 188A, RG 316

Body Features

Body Plating Material	Tin
-----------------------	-----

Contact Features

Ferrule Material	Copper
Ferrule Plating Material	Tin

Dimensions

Ferrule Inside Diameter	2.84 mm [.112 in]
Accepts Wire Insulation Diameter Range	2.84 mm [.112 in]

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

[Product Drawings](#)
[FERRULE, SUB MIN](#)



English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-332056-0_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-332056-0_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-332056-0_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

COAXICON Contacts

English

Coaxial Contacts

English

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Product Specifications

Product Specification

English

Product Environmental Compliance

[MD_1-332056-0_07082014050_dmtec](#)

English

[MD_1-332056-0_07082014050_dmtec](#)

English

Instruction Sheets

Instruction Sheet (U.S.)

English

[Series SMC Dual Crimp Type COAXICON Connectors](#)

English

Agency Approvals

Agency Approval Document

English

1-332056-0

RF Connector Ferrules, RG 174 / RG 188A / Belden 9221, Ferrule Inside Diameter 2.84 mm [.112 in], Copper, Tin Plating

