

1-350778-1 ✓ ACTIVE

MATE-N-LOK | Universal MATE-N-LOK


TE Internal #: 1-350778-1

Rectangular Power Connectors, Housing, Receptacle, Wire-to-Wire / Wire-to-Panel, 2 Position, 6.35 mm [.25 in] Centerline, Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Panel, Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **6.35 mm [.25 in]**

## Features

### Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	2
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

### Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

### Contact Features

Contact Layout	Inline
----------------	--------



Multiple Contact Types	Without
Contact Retention Within Housing	Without
Contact Type	Pin

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Patch & Tabs
Connector Mounting Type	Panel Mount

#### Housing Features

Centerline (Pitch)	6.35 mm [.25 in]
Housing Color	Brown
Housing Material	Nylon

#### Dimensions

Panel Thickness	.76 – 2.29 mm [.03 – .09 in]
-----------------	------------------------------

#### Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

#### Operation/Application

Assembly Integration Feature	Without
Circuit Application	Power & Signal

#### Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189
VDE Tested	Yes

#### Packaging Features

Packaging Method	Package
------------------	---------



Packaging Quantity 1

**Other**

For Use With	Appropriate Universal MATE-N-LOK Plug
--------------	---------------------------------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

















EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**


 <p>TE Part # 640309-6 UMNL PIN 12-10 AU/PHBZ</p>	 <p>TE Part # 350551-6 UMNL SOK 20-14 AU/PHBZ L/P</p>	 <p>TE Part # 350690-2 UMNL PIN 24-18 AUBR L/P</p>	 <p>TE Part # 926902-3 UNIV-MNL SPLIT ST</p>
--	--	---	---

 TE Part # 350550-7 UMNL SOK 20-14 AU/BR L/P	 TE Part # 350690-3 UMNL PIN 24-18 PTPPHBZ L/P	 TE Part # 350689-7 UMNL SOK 24-18 AUBR L/P	 TE Part # 350547-7 UMNL PIN 20-14 AUBR L/P
 TE Part # 350689-2 UMNL SOK 24-18 AUBR L/P	 TE Part # 640310-3 UMNL SOK 12-10 PTPPHBZ	 TE Part # 350689-3 UMNL SOK 24-18 PTPPHBZ L/P	 TE Part # 350690-7 UMNL PIN 24-18 AUBR L/P
 TE Part # 350689-1 UMNL SOK 24-18 PTPBR L/P	 TE Part # 926893-3 UNIV.M-N-L.SOCKET	 TE Part # 350550-6 UMNL SOK 20-14 AU/PHBZ L/P	 TE Part # 350547-3 UMNL PIN 20-14 PTPPHBZ L/P
 TE Part # 350551-7 UMNL SOK 20-14 AU/BR L/P	 TE Part # 350550-2 UMNL SOK 20-14 AU/BR L/P	 TE Part # 770672-1 UMNL PIN 30-26 PTPBR L/P	 TE Part # 350547-6 UMNL PIN 20-14 AU/PHBZ L/P


Also in the Series | **Universal MATE-N-LOK**

 Circular Power Connectors(2)	 Connector Contacts(11)	 Insertion & Extraction Tools(4)	 Power Contacts(207)
---	--	--	--





Rectangular Boots &amp; Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(728)

## Documents

### Product Drawings

[02P UMNL V0 CAP HSG BROWN](#)

English

### CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_1-350778-1\\_V1.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1-350778-1\\_V1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1-350778-1\\_V1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_SOCKET\\_CONNECTORS\\_STANDARD\\_DENSITY](#)

English

### Product Specifications

[Application Specification](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)



English

---

[Agency Approvals](#)

[CSA Certificate](#)

English