



AMP

TE Internal #: 1-350522-9

Rectangular Boots & Strain Relief, Strain Relief, Nylon, Black, 9

Position, -67 – 185 °F [-55 – 85 °C]

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Boots & Strain Relief



Protection & Strain Relief Accessory Type: **Strain Relief**

Primary Product Material: **Nylon**

Primary Product Color: **Black**

Number of Positions: **9**

Sealable: **No**

Features

Product Type Features

| | |
|---|---------------|
| Protection & Strain Relief Accessory Type | Strain Relief |
| Sealable | No |
| Product Type | Accessory |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 9 |
|---------------------|---|

Body Features

| | |
|--------------------------|-------|
| Primary Product Material | Nylon |
| Primary Product Color | Black |

Usage Conditions

| | |
|-----------------------------|---------------------------|
| Operating Temperature Range | -55 – 85 °C[-67 – 185 °F] |
|-----------------------------|---------------------------|

Industry Standards

| | |
|-----------------|---------|
| Agency/Standard | CSA, UL |
|-----------------|---------|

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|



Packaging Quantity 100

Other

Comment One piece - Clam Shell.

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

09P MR STR/REL HNG BLK

English

CAD Files

Customer View Model

[ENG_CVM_1-350522-9_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-350522-9_K.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-350522-9_K.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-350522-9_AC.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-350522-9_AC.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-350522-9_AC.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP* MINIATURE RECTANGULAR II (MRII) CONNECTORS

English

1-350522-9

Rectangular Boots & Strain Relief, Strain Relief, Nylon, Black, 9 Position, -67 – 185 °F
[-55 – 85 °C]

