

1-47387-0 ✓ ACTIVE

AMP | B&H BET, PIDG


TE Internal #: 1-47387-0

Hand Crimping Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-), B&H BET

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

Power Technology Type: **Battery (110v), Battery (220v)**

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
Power Technology Type	Battery (110v), Battery (220v)
Tooling Type	Double Action Hand Tool, Head Assembly

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CAT-P592-R472A  
PIDG RING TONGUE TERMINALS



TE Part # CAT-P592-SP118  
PIDG Spade Tongue Terminals



TE Part # 327583  
SPLICE BUTT PIDG 16-14/22-18



TE Part # CAT-P592-F614  
PIDG Flanged Spade Tongue Terminals



TE Part # CAT-P592-R2456  
PIDG Rectangular Tongue Terminals



TE Part # 324227  
PG SHUR PLUG 16-14



TE Part # 326741  
TERMINAL,PG SPD 16-14 8



TE Part # 322994  
TERMINAL,PG SPD 16-14 6



TE Part # 735159  
250 PIDG FF



TE Part # 324165  
TERMINAL,PG SPD FLG 16-14 6



TE Part # 324228  
PG SHUR PLUG 16-14



TE Part # 327748  
TAB,PIDG 16-14




TE Part # 328527  
TERMINAL,PG R 16-14 8



TE Part # 328308  
SPARE WIRE CAP,BLU, 16-14 AWG



TE Part # 1SET121084R0000  
RT025-020-N



TE Part # 1SET121085R0000  
RT025-04S-N



TE Part # 1SET121086R0000  
RT025-035-N



TE Part # 1SET121090R0000  
RT025-060-N




TE Part # 1SET121091R0000  
RT025-080-N




TE Part # 1SET121092R0000  
RT025-38S-N

Also in the Series | **B&H BET**




Hand Crimping Tools(1)




Mechanical Connectors(5)

Also in the Series | **PIDG**




Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)



Knife Disconnects(11)



PCB Terminals(9)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(861)



Special Purpose Terminals(1)



Splices(48)

## Documents

### Datasheets & Catalog Pages

[ENG\\_CS\\_1-1773859-6\\_0915](#)

English

### Bottoming Dies

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English