

2061980-5 ✓ ACTIVE

## FullAXS Mini

TE Internal #: 2061980-5

Rugged Fiber Cable Assemblies, Fiber Optic Cable (FOCAB), .189 in [4.8 mm] Diameter, 2 Fibers, Blue, Blue, Black Cable Color, FullAXS Mini

[View on TE.com >](#)



Fiber Optics > Fiber Optic Cable Assemblies > Rugged Fiber Cable Assemblies



Fiber Optic Cable Type: **Fiber Optic Cable (FOCAB)**

Cable Assembly Fiber Diameter: **9/125  $\mu$ m**

Outside Cable Diameter: **4.8 mm [ .189 in ]**

Number of Fibers: **2**

Connector Color (End A): **Blue**

## Features

### Product Type Features

Rugged Fiber Cable Assembly System	FullAXS Mini
Fiber Optic Cable Type	Fiber Optic Cable (FOCAB)
Fiber Optic Mode	Singlemode
Connector Type (End A)	FULLAXS MINI LC Duplex Plug
Connector Type (End B)	LC Duplex Plug
Cable Assembly Type	FULLAXS MINI LC Duplex to LC Duplex
Fiber Type	SM

### Configuration Features

Number of Fibers	2
Cable Buffering	Semi-Tight Buffer

### Body Features

Connector Color (End A)	Blue
Connector Color (End B)	Blue
Cable Color	Black
Boot Type (Right)	Bend Limiting
Boot Color (Left)	Blue
Boot Color (Right)	Blue



### Dimensions

Cable Assembly Fiber Diameter	9/125 $\mu$ m
Outside Cable Diameter	4.8 mm[.189 in]

### Other

Cable Assembly Length	5 m
-----------------------	-----

### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Also in the Series | FullAXS Mini



### Documents

#### Product Drawings

[FOSM GLARO LEAD 4.8 MM FXS MINI 5 M](#)

English

#### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2061980-5\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2061980-5\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2061980-5\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

#### Datasheets & Catalog Pages

[FullAXS Brochure \(English\)](#)

English

#### Product Specifications

[Product Specification](#)

English

2061980-5

Rugged Fiber Cable Assemblies, Fiber Optic Cable (FOCAB), .189 in [4.8 mm]  
Diameter, 2 Fibers, Blue, Blue, Black Cable Color, FullAXS Mini

