



Alcoswitch | Alcoswitch AV22

TE Internal #: 2213771-7

Push Button Switches, Double Pole - Double Throw Configuration (Pole-Throw), Anti-Vandal, Single Actuator, Flush Actuator Profile, Alcoswitch AV22

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Push Button Switches



Configuration (Pole-Throw): **Double Pole - Double Throw**

Push Button Switch Product Type: **Anti-Vandal**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

| | |
|---------------------------------|-------------|
| Switch Type | Pushbutton |
| Dust Proof | Yes |
| Push Button Switch Product Type | Anti-Vandal |
| Illuminated | No |
| Actuator Style | Round |

Configuration Features

| | |
|----------------------------|----------------------------|
| ESD Grounding Terminal | Without |
| Detent Style | Audible |
| Configuration (Pole-Throw) | Double Pole - Double Throw |
| Number of Actuators | Single |
| Snap Action | Without |
| Support Bracket | Without |
| Tactile | No |
| Operating Function | Push-On/Push-Off |

Electrical Characteristics

| | |
|-----------------------------------|---------|
| Push Button Switch Voltage Rating | 250 VAC |
|-----------------------------------|---------|

Body Features

| | |
|--|--|
| | |
|--|--|



| | |
|------------------|----------|
| Case Material | PBT |
| Actuator Profile | Flush |
| Bushing Style | Threaded |

Contact Features

| | |
|---|--------|
| Push Button Switch Contact Current Rating | 5 A |
| Switch Contact Plating Material | Silver |

Termination Features

| | |
|------------------|-----------|
| Termination Type | Wire Lugs |
|------------------|-----------|

Mechanical Attachment

| | |
|----------------------------------|----------|
| Mounting Angle | Vertical |
| Push Button Switch Mounting Type | Panel |

Housing Features

| | |
|----------------|-----|
| Process Sealed | Yes |
|----------------|-----|

Dimensions

| | |
|--|-------|
| | 22 in |
|--|-------|

Industry Standards

| | |
|-----------|------|
| IP Rating | IP67 |
|-----------|------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Alcoswitch AV22



Documents

Product Drawings
AV22 DPL 5A NO LED

English

CAD Files



Customer View Model

[ENG_CVM_CVM_2213771-7_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213771-7_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213771-7_A1.2d_dxf.zip](#)

English

[3D PDF](#)

[3D](#)

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English