



Application Tooling > Hand Crimping Tools



Die Sets Type: **Fixed In Tool**

TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Tooling Type: **Hand Tool**

### Features

#### Other

Die Sets Type	Fixed In Tool
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Hand Tool

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



TE Part # CAT-AM71-T98B  
Strip Pin and Socket Contacts, Type III



TE Part # CAT-M5833-C8684A  
CRIMP CONTACTS



TE Part # CAT-035-DCCPB20  
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



TE Part # CAT-035-DCCSC20  
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



TE Part # CAT-AM71-T98F  
TYPE III CONTACTS STRIP HIGH CURRENT



TE Part # CAT-D9934-A75  
DYNAMIC 3000 CONTACT



TE Part # CAT-AM7017-C7671  
AMP COMMON TERMINATION CONTACTS



TE Part # CAT-F439-P65254  
2.54mm FFC Connectors Pin Contacts



TE Part # CAT-038-DCCSC22  
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 22



TE Part # CAT-AM71-T98C  
Strip Pin and Socket Contacts, Type III, EMEA



TE Part # CAT-103156-WTBCC  
Wire-to-Board Connector Contacts: socket, wire size 30-16 AWG, SL 156



TE Part # CAT-AM74-H3401E  
HE13/HE14 Contacts



TE Part # CAT-AM7801-T273  
Contacts: Size 16, 13A



TE Part # CAT-038-DCCPB22  
D-Sub Connector Contacts: Pin, Brass, Signal, Size 22



TE Part # CAT-D9934-A15  
Contact: Component To Wire; 3-5A, 30-18 wire size



TE Part # 1734597-1  
1.0 WTB Terminal, Receptacle



## Documents

### Datasheets & Catalog Pages

#### Bottoming Dies

English

### Instruction Sheets

#### Instruction Sheet (U.S.)

English