



Push Splice Push Grip

TE Internal #: 2324697-2

Splices, 22 – 12 AWG Wire Size, .5 – 2.5 mm² Wire Size, Splice Capacity 2, Standard, Yellow - Translucent, Push Splice Push Grip

[View on TE.com >](#)

Terminals & Splices > Splices



Wire Size: .5 – 2.5 mm²

Sealable: **No**

Splice Capacity: **2**

Splice Features: **Standard**

Features

Product Type Features

Sealable	No
Splice Type	Closed End Splice
Serrated	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Splice Capacity	2
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Voltage (Max)	600 VAC
Operating Voltage	450V (IEC) / 600V (UL)
Current Rating	24 A

Body Features

Splice Features	Standard
Primary Product Color	Yellow - Translucent



Contact Features

Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.5 – 2.5 mm ²
-----------	--------------------------

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Agency/Standard	IEC, UL
Agency/Standard Number	IEC 60988-2-2, UL 486C
Government Qualified Splice	No

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Product Compliance

















[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-L97-L4981 Z50 ZHAGA PROFILE LED HOLDERS</p>	 <p>TE Part # CAT-L97-L4981A Z50 LOW PROFILE LED HOLDERS</p>	 <p>TE Part # CAT-L97-L4981D Mini LED Holders Z32</p>	 <p>TE Part # CAT-L97-L4981B Z45 LED HOLDERS</p>
 <p>TE Part # CR2103-000 CPGI-WC-WG-OR-BULK</p>	 <p>TE Part # 2174024-1 LUMAWISE LED HOLDER, TYPE NL2</p>	 <p>TE Part # CR2105-000 CPGI-WC-WG-YW-BULK</p>	 <p>TE Part # 1811027-1 ASSEMBLY,12AWG TAP</p>
 <p>TE Part # 1811027-2 ASSEMBLY,18AWG TAP</p>	 <p>TE Part # 1-2154857-3 Socket, SCALABLE LED, 2PC, Tin</p>	 <p>TE Part # 2-2154857-1 Socket, SCALABLE LED, 2PC, Gold, w /TS</p>	 <p>TE Part # 2134318-1 LUMAWISE LED HOLDER, TYPE LUMIPACK N1</p>
 <p>TE Part # 2271203-1 2PIN WIRE TO WIRE CONNECTOR</p>	 <p>TE Part # CR2102-000 CPGI-WC-WG-GR-BULK</p>	 <p>TE Part # CR2100-000 CPGI-WC-TG-TN-BULK</p>	 <p>TE Part # 3-2154857-3 Socket, SCALABLE LED, 2PC, Tin, w/TS</p>



Also in the Series | Push Splice Push Grip



Documents

Product Drawings

PUSH GRIP CONNECTOR 2P

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2324697-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2324697-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2324697-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

COMPACT PUSH GRIP WIRE CONNECTORS

English

Product Specifications

Application Specification

English



Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

FIMKO Certificate

English